

Converter - MCR-DAC 8-I- 4-BUS - 2808226

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




MCR 8-bit digital/analog converters, with flat-ribbon cable connection and COMBICON connector, pitch 5.08 mm, output signal 4..20 mA

The illustration shows version MCR-DAC 8-U-5-BUS



Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 075576
Weight per Piece (excluding packing)	144.5 g
Custom tariff number	85389091
Country of origin	Germany

Technical data

Dimensions

Width	25 mm
Height	79 mm
Depth	93 mm

Ambient conditions

Ambient temperature (operation)	0 °C ... 55 °C
---------------------------------	----------------

Input data

Input signal	8 Bit (1 leading sign)
Input voltage range	24 V DC ... 30 V DC
Signal level "1" signal	≥ 15 V DC
Signal level "0" signal	≤ 2 V DC

Converter - MCR-DAC 8-I- 4-BUS - 2808226

Technical data

Input data

Max. input current	$\leq 1 \text{ mA}$
Input resistance	$\geq 5.7 \text{ k}\Omega$
Type of protection	Surge protection
Protective circuit/component	Suppressor diode, 36 V / 1500 W

Output data

Output current	5 mA
Output name	Current output
Current output signal	4 mA ... 20 mA
Load/output load current output	$\leq 500 \Omega$
Resolution, outputs (current)	63 μA
D/A conversion time	$\leq 50 \mu\text{s}$

Power supply

Nominal supply voltage	24 V DC $\pm 10 \%$
Supply voltage range	22 V DC ... 26 V DC
Max. current consumption	20 mA

Connection data

Connection method	Flat-ribbon cable connection and COMBICON connector (pitch 5.08 mm)
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section AWG min.	24
Conductor cross section AWG max.	14
Conductor cross section flexible min.	0.2 mm ²
Conductor cross section flexible max.	2.5 mm ²
Stripping length	8 mm
Screw thread	M3

General

Maximum transmission error	$\pm 1 \text{ LSB}$, for 25°C
Protective circuit	Protection against polarity reversal, suppressor diode
Color	green
Housing material	Polyamide PA non-reinforced
Mounting position	any
Conformance	CE-compliant

Standards and Regulations

Conformance	CE-compliant
-------------	--------------

Converter - MCR-DAC 8-I- 4-BUS - 2808226

Classifications

eCl@ss

eCl@ss 4.0	27230208
eCl@ss 4.1	27230208
eCl@ss 5.0	27230208
eCl@ss 5.1	27230208
eCl@ss 6.0	27230208
eCl@ss 7.0	27230208
eCl@ss 8.0	19179290

ETIM

ETIM 2.0	EC001440
ETIM 3.0	EC001440
ETIM 4.0	EC001440
ETIM 5.0	EC000310

UNSPSC

UNSPSC 6.01	30211506
UNSPSC 7.0901	39121008
UNSPSC 11	39121008
UNSPSC 12.01	39121008
UNSPSC 13.2	39121008

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted


Approval details

EAC

Converter - MCR-DAC 8-I- 4-BUS - 2808226

Drawings

Dimensional drawing



Circuit diagram

