

Upper part of housing - EH 90 F-C SS/ABS BK9005 - 2201388

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




DIN rail housing, Upper part, flat design, One-way connection opening, with vents, width: 90.1 mm, height: 74.65 mm, depth: 36.95 mm, color: black (9005)

Your advantages

- ✓ DIN rail or wall mounting for application-specific device attachment
- ✓ Easy design-in, thanks to variable housing form factor
- ✓ Complete flexibility, thanks to PCBs with horizontal, frontal, and orthogonal orientation to the front of the device
- ✓ Three cover versions for individual PCB connections
- ✓ Integration of a wide variety of PCB connection technologies for a functional device design



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 046356 911207
GTIN	4046356911207
Weight per Piece (excluding packing)	36.000 g
Custom tariff number	85472000
Country of origin	India

Technical data

Item properties

Brief article description	Upper part of housing
Type	EH 90 F-C SS/ABS BK9005
Order No.	2201388
Housing type	DIN rail housing

Upper part of housing - EH 90 F-C SS/ABS BK9005 - 2201388

Technical data

Item properties

Housing series	EH
Type	Upper part, flat design
Max. IP code to attain	IP20
Mounting type	Snap in
Ventilation openings present	yes

Dimensions

Width [w]	90.1 mm
Height [h]	74.65 mm
Depth [d]	36.95 mm
Depth from base support surface [d]	19.95 mm

Material data

Color (RAL)	black (9005)
Flammability rating according to UL 94	HB
Housing material	ABS

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 80 °C
Ambient temperature (operation)	-40 °C ... 80 °C (depending on power dissipation)

PCB data

Mounting position	Vertical (horizontal DIN rail)
Type of PCB mount	Latching

Packaging information

Pieces per package	10
Denomination packing units	Pcs.

Standards and regulations

Flammability rating according to UL 94	HB
--	----


Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Upper part of housing - EH 90 F-C SS/ABS BK9005 - 2201388

Dimensional drawing



Classifications

eCl@ss

eCl@ss 10.0.1	27182702
eCl@ss 5.0	27180500
eCl@ss 5.1	27180500
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

ETIM

ETIM 4.0	EC001031
ETIM 5.0	EC001031

Upper part of housing - EH 90 F-C SS/ABS BK9005 - 2201388

Classifications

ETIM

ETIM 6.0	EC001031
ETIM 7.0	EC001031

UNSPSC

UNSPSC 13.2	31261501
UNSPSC 18.0	31261501
UNSPSC 19.0	31261501
UNSPSC 20.0	31261501
UNSPSC 21.0	31261501

Accessories

Accessories

Filler plug

Filler plugs - EH 22,5 F-FP/ABS BK9005 - 2201845



DIN rail housing, Filler plug for unoccupied terminal points, with vents, width: 21.35 mm, height: 13.67 mm, depth: 33.39 mm, color: black (9005)

Filler plugs - EH 22,5 F-FP/ABS GY7035 - 2201844



DIN rail housing, Filler plug for unoccupied terminal points, with vents, width: 21.35 mm, height: 13.67 mm, depth: 33.39 mm, color: light gray (7035)

Necessary add-on products

Feed-through header - MSTBV 2,5/17-G - 1753738



PCB headers, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 17, pitch: 5 mm, color: green, contact surface: Tin, mounting: Wave soldering, pin layout: Linear pinning, solder pin [P]: 3.9 mm

Upper part of housing - EH 90 F-C SS/ABS BK9005 - 2201388

Accessories

Feed-through header - MSTBV 2,5/17-G-5,08 - 1758160



PCB headers, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 2.5 mm², number of positions: 17, pitch: 5.08 mm, color: green, contact surface: Tin, mounting: Wave soldering, pin layout: Linear pinning, solder pin [P]: 3.9 mm

Pin strip - PST 1,3/17-5,0 - 1935556



Pin strip, nominal current: 12 A, rated voltage (III/2): 320 V, nominal cross section: 1.5 mm², number of positions: 17, pitch: 5 mm, color: black, contact surface: Tin, mounting: THR soldering, pin layout: Linear pinning, solder pin [P]: 3.5 mm, The maximum current depends on the plug used. The lower of the two current values apply for plug and pin strip. The pin strip is made of highly temperature resistant plastic and is thus suitable for the reflow process.