

Antenna cable - RAD-CAB-PFP400-80 - 2867393

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Antenna cable, outside diameter: 10 mm (0.4 in.), inner conductor: solid, attenuation: 3.3 / 5.6 / 8.4 dB at 0.9 / 2.4 / 5.8 GHz, connection: 2x N (male), cable length: 24 m (80 ft.)



Your advantages

- Low attenuation
- UV resistant
- For outdoor installation

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 931766
GTIN	4017918931766
Weight per Piece (excluding packing)	2,630.840 g
Custom tariff number	85442000
Country of origin	China

Technical data

Dimensions

Fixed cable length	24 m
External diameter	10.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

General

Antenna cable - RAD-CAB-PFP400-80 - 2867393

Technical data

General

Connection 1	Connector connection
Connection method	Type N (male)
Note	Both sides
Cable type	PFP-400
Outer sheath, material	PE
External sheath, color	black
Minimum bending radius	25.00 mm
Frequency range	400 MHz ... 5.8 GHz
Impedance	50 Ω

Attenuation

868 / 900 MHz	3.3 dB
2.4 GHz	5.6 dB
5 GHz	8.4 dB

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	27060800
eCl@ss 4.1	27060800
eCl@ss 5.0	27061800
eCl@ss 5.1	27061800
eCl@ss 6.0	27061800
eCl@ss 7.0	27061805
eCl@ss 8.0	27060310
eCl@ss 9.0	27060310

ETIM

ETIM 2.0	EC000019
ETIM 3.0	EC000019
ETIM 4.0	EC000019
ETIM 5.0	EC001682
ETIM 6.0	EC001682
ETIM 7.0	EC001682

Antenna cable - RAD-CAB-PFP400-80 - 2867393

Classifications

UNSPSC

UNSPSC 6.01	26121608
UNSPSC 7.0901	26121608
UNSPSC 11	26121608
UNSPSC 12.01	26121608
UNSPSC 13.2	26121606