

Industrial Ethernet Switch - FL SWITCH 2206-2FX ST - 2702332

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Managed Switch 2000, 6 RJ45 ports 10/100 Mbps, 2 ST multi-mode 100 Mbps, Degree of protection IP20

Why buy this product

- Unmanaged Mode
- Configuration memory
- RSTP
- DHCP client, DHCP server (pool-based and port-based), DHCP option 82
- VLANs
- MRP (client and master)
- Web-based management, SNMP
- Slim design
- 40°C ... +70°C ambient temperature

Ethernet

Key Commercial Data

Packing unit	1
GTIN	 4 055626 128597
GTIN	4055626128597
Custom tariff number	85176200

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	45 mm
Height	130 mm

Industrial Ethernet Switch - FL SWITCH 2206-2FX ST - 2702332

Technical data

Dimensions

Depth	115 mm
-------	--------

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)
Air pressure (operation)	68 kPa ... 108 kPa (3000 m above sea level)
Air pressure (storage/transport)	68 kPa ... 108 kPa (3000 m above sea level)

Interfaces

Interface 1	Ethernet (RJ45)
No. of ports	6 (RJ45 ports)
Connection method	RJ45
Note on connection method	Auto negotiation and autocrossing
Transmission physics	Copper
Transmission speed	10/100 Mbps
Transmission length	100 m (per segment)
Signal LEDs	Data receive, link status
Interface 2	Ethernet FO
No. of ports	2 (ST multi-mode)
Connection method	ST
Transmission physics	multi-mode fiberglass
Transmission speed	100 Mbps (full duplex)
Transmission length	11000 m (fiberglass with F-G 62.5/125 0.7 dB/km F1000)
	6400 m (fiberglass with F-G 50/125 0.7 dB/km F1200)
	3000 m (fiberglass with F-G 62.5/125 2.6 dB/km F600)
	2800 m (fiberglass with F-G 50/125 1.6 dB/km F800)
Wavelength	1300 nm
Signal LEDs	Data receive, link status

Function

Basic functions	Store-and-forward switch, complies with IEEE 802.3
Management	Web-based management (HTTP/HTTPS)
	SNMPv1/v2/v3
	Command-line interface (Telnet, SSH)
Diagnostic functions	RMON History
	LLDP (Link Layer Discovery Protocol)

Industrial Ethernet Switch - FL SWITCH 2206-2FX ST - 2702332

Technical data

Function

	SNMP-Traps
	N:1-Portmirroring
	ACD (Address Conflict Detection)
Filter functions	Quality of Service (4 priority classes)
	Port-Priorisierung
	VLAN (up to 32 VLANs)
	IGMP Snooping (32 groups)
	IGMP Query
	Auto-Query-Port
	Extended Multicast Filtering
MAC address table	8k
Redundancy	MRP (Media Redundancy Protocol)
	RSTP (Rapid Spanning Tree Protocol)
	FRD (Fast Ring Detection)
	Large Tree Support
IP parameterization	DHCP-Client
	DHCP Option 82 (Relay Agent)
	DHCP server (pool-based, port-based)
	BootP
PROFINET IO conformance class	Conformance-Class A
Status and diagnostic indicators	LEDs: US1, US2 (power supply), Fail (alarm contact), 2 LEDs per Ethernet port (Link/Activity and Speed)
Signal contact control voltage	24 V DC (typical)
Signal contact control current	200 mA (1 minute, maximum)

Network expansion parameters

Cascading depth	Network, linear, and star structure: any
Maximum conductor length (twisted pair)	100 m

Supply voltage

Supply voltage	24 V DC (redundant)
Residual ripple	3.6 V _{PP} (within the permitted voltage range)
Supply voltage range	9 V DC ... 57 V DC
Typical current consumption	255 mA (at U _S = 24 V DC)
Current consumption	260 mA

General

Mounting type	DIN rail
Type AX	Book type

Industrial Ethernet Switch - FL SWITCH 2206-2FX ST - 2702332

Technical data

General

Net weight	260 g
Housing material	Polycarbonate fiber reinforced
MTTF	343.16 Years (SN 29500 standard, temperature 25 °C, operating cycle 21 % (5 days a week, 8 hours a day))
	153.37 Years (SN 29500 standard, temperature 40 °C, operating cycle 34.25 % (5 days a week, 12 hours a day))
	18.66 Years (SN 29500 standard, temperature 70 °C, operating cycle 100 % (7 days a week, 24 hours a day))

Connection data

Connection method	Screw connection
Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section flexible min.	0.14 mm ²
Conductor cross section flexible max.	1.5 mm ²
Conductor cross section AWG min.	26
Conductor cross section AWG max.	16
Stripping length	9 mm

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Developed in acc. with standard	IEC 61000-6.2
Test standard	IEC 61000-4-2 (ESD)
Test result	Criterion B
Test standard	EN 61000-4-3 (electromagnetic fields)
Test result	Criterion A
Test standard	IEC 61000-4-4 (burst)
Test result	Criterion A
Test standard	IEC 61000-4-5 (surge)
Test result	Criterion A
Test standard	IEC 61000-4-6 (immunity to conducted interference)
Test result	Criterion A
Noise emission	EN 61000-6-4
Noise immunity	EN 61000-6-2
Vibration (storage/transport)	5g, 150 Hz, in acc. with IEC 60068-2-6
Free from substances that could impair the application of coating	Yes
Vibration (operation)	In acc. with IEC 60068-2-6: 5g, 150 Hz
ATEX	# II 3G Ex nA IIC T4 Gc
IECEX	Ex nA IIC T4 Gc

Industrial Ethernet Switch - FL SWITCH 2206-2FX ST - 2702332

Technical data

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	27250501
eCl@ss 4.1	27250501
eCl@ss 5.0	27250501
eCl@ss 5.1	27250501
eCl@ss 6.0	27250501
eCl@ss 7.0	27250501
eCl@ss 8.0	19170106
eCl@ss 9.0	19170106

ETIM

ETIM 3.0	EC000734
ETIM 4.0	EC000734
ETIM 5.0	EC000734

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	43222612

Approvals

Approvals

Approvals

ABS / EAC / UL Listed / cUL Listed / cULus Listed

Ex Approvals

IECEX / ATEX / UL Listed / cUL Listed / cULus Listed

Industrial Ethernet Switch - FL SWITCH 2206-2FX ST - 2702332

Approvals

Approval details

ABS	http://www.eagle.org/eagleExternalPortalWEB/	17-HG1592765-PDA
-----	---	------------------

EAC		RU C-DE.A*30.B00767
-----	--	---------------------

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
-----------	--	---	---------------

cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
------------	--	---	---------------

cULus Listed			
--------------	--	--	--

Accessories

Accessories

Assembly adapter

Adapter - FL DIN RA - 2891053

The FL DIN RA is installed in a standard, 19-inch rack (EIA-310-D, IEC 60297-3-100) to allow DIN rail mounted equipment to be rack mounted.



Drivers and interfaces

Software - FL SNMP OPC AGENT V3 - 2701136



SNMP-OPC agent, German and English, for integrating OPC-based automation solutions in company-wide network management systems

Industrial Ethernet Switch - FL SWITCH 2206-2FX ST - 2702332

Accessories

Software - FL SNMP OPC SERVER V3 - 2701139



SNMP-OPC server, German and English, for monitoring and configuration of SNMP-capable equipment in HMI and SCADA systems

End block

End clamp - E/NS 35 N - 0800886



End clamp, width: 9.5 mm, color: gray

Network management software

Software - FL VIEW 32 LITE - 2701744



FL VIEW, SNMP-based software in English, for the detection and display of Ethernet networks. 32 nodes (network devices) can be monitored in one Class C subnetwork with this version.

Parameterization memory

Memory - SD FLASH 512MB - 2988146



Program and configuration memory, plug-in, 512 Mbyte.

Industrial Ethernet Switch - FL SWITCH 2206-2FX ST - 2702332

Accessories

Program / configuration memory - SD FLASH 2GB - 2988162



Program and configuration memory

Protective cap

Dust protection - FL RJ45 PROTECT CAP - 2832991



Dust protection caps for RJ45 socket

Software - IPASSIGN - 2701094



IPAssign is an easy to use tool for setting the IP address of devices which rely on BOOTP. No installation or administrative rights are required to use IPAssign.

This product is free and only available from the "Downloads" tab.

Printed-circuit board connector - FK-MCP 1,5/ 5-ST-3,81 GY - 1884005

Plug component, Nominal current: 8 A, Rated voltage (III/2): 160 V, Number of positions: 5, Pitch: 3.81 mm, Connection method: Push-in spring connection, Color: gray, Contact surface: Tin
