

## Industrial Ethernet Switch - FL SWITCH 2308 - 2702652

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Managed Switch 2000, 8 RJ45 ports 10/100/1000 Mbps, Degree of protection IP20


### Why buy this product

- Unmanaged Mode
- Configuration memory
- RSTP
- DHCP client, DHCP server (pool-based and port-based), DHCP option 82
- VLANs
- MRP (client and master)
- Web-based management, SNMP
- Slim design
- 40°C ... +70°C ambient temperature

RoHS

Ethernet

### Key Commercial Data

Packing unit	1
GTIN	 4 055626 259987
GTIN	4055626259987

### Technical data

#### Dimensions

Width	45 mm
Height	130 mm
Depth	115 mm

#### Ambient conditions

# Industrial Ethernet Switch - FL SWITCH 2308 - 2702652

## Technical data

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)
Air pressure (operation)	53 kPa ... 108 kPa (5000 m above sea level)
Air pressure (storage/transport)	53 kPa ... 108 kPa (5000 m above sea level)

### Interfaces

Interface 1	Ethernet (RJ45)
No. of ports	8 (RJ45 ports)
Connection method	RJ45
Note on connection method	Auto negotiation and autocrossing
Transmission physics	Copper
Transmission speed	10/100/1000 Mbps
Transmission length	100 m (per segment)
Signal LEDs	Data receive, link status

### Function

Basic functions	Store-and-forward switch, complies with IEEE 802.3
Management	Web-based management (HTTP/HTTPS)
	SNMPv1/v2/v3
	Command-line interface (Telnet, SSH)
Diagnostic functions	RMON History
	LLDP (Link Layer Discovery Protocol)
	SNMP-Traps
	N:1-Portmirroring
	ACD (Address Conflict Detection)
Filter functions	Quality of Service (4 priority classes)
	Port-Priorisierung
	VLAN (up to 32 VLANs)
	IGMP Snooping (32 groups)
	IGMP Query
	Auto-Query-Port
	Extended Multicast Filtering
MAC address table	8k
Redundancy	MRP (Media Redundancy Protocol)
	RSTP (Rapid Spanning Tree Protocol)

# Industrial Ethernet Switch - FL SWITCH 2308 - 2702652

## Technical data

### Function

	FRD (Fast Ring Detection)
	Large Tree Support
IP parameterization	DHCP-Client
	DHCP Option 82 (Relay Agent)
	DHCP server (pool-based, port-based)
	BootP
PROFINET IO conformance class	Conformance-Class A
Status and diagnostic indicators	LEDs: US1, US2 (power supply), Fail (alarm contact), 2 LEDs per Ethernet port (Link/Activity and Speed)
Signal contact control voltage	24 V DC (typical)
Signal contact control current	200 mA (1 minute, maximum)

### Network expansion parameters

Cascading depth	Network, linear, and star structure: any
Maximum conductor length (twisted pair)	100 m

### Supply voltage

Supply voltage	24 V DC (redundant)
Residual ripple	3.6 V <sub>pp</sub> (within the permitted voltage range)
Supply voltage range	12 V DC ... 57 V DC
Typical current consumption	280 mA (at U <sub>S</sub> = 24 V DC)
Current consumption	280 mA

### General

Mounting type	DIN rail
Type AX	Book type
Net weight	0 g
Housing material	Polycarbonate fiber reinforced

### Connection data

Connection method	Screw connection
Conductor cross section solid min.	0.14 mm <sup>2</sup>
Conductor cross section solid max.	1.5 mm <sup>2</sup>
Conductor cross section flexible min.	0.14 mm <sup>2</sup>
Conductor cross section flexible max.	1.5 mm <sup>2</sup>
Conductor cross section AWG min.	26
Conductor cross section AWG max.	16
Stripping length	9 mm

### Standards and Regulations

# Industrial Ethernet Switch - FL SWITCH 2308 - 2702652

## Technical data

### Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Developed in acc. with standard	IEC 61000-6.2
Test standard	IEC 61000-4-2 (ESD)
Test result	Criterion B
Test standard	EN 61000-4-3 (electromagnetic fields)
Test result	Criterion A
Test standard	IEC 61000-4-4 (burst)
Test result	Criterion A
Test standard	IEC 61000-4-5 (surge)
Test result	Criterion A
Test standard	IEC 61000-4-6 (immunity to conducted interference)
Test result	Criterion A
Noise emission	EN 61000-6-4
Noise immunity	EN 61000-6-2
Vibration (storage/transport)	5g, 150 Hz, in acc. with IEC 60068-2-6
Free from substances that could impair the application of coating	Yes
Vibration (operation)	In acc. with IEC 60068-2-6: 5g, 150 Hz
ATEX	# II 3G Ex nA IIC T4 Gc
IECEX	Ex nA IIC T4 Gc

### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Approvals

### Approvals

Approvals

ABS / EAC

Ex Approvals

### Approval details

ABS	<a href="http://www.eagle.org/eagleExternalPortalWEB/">http://www.eagle.org/eagleExternalPortalWEB/</a>	17-HG1592765-PDA
-----	---	------------------

## Industrial Ethernet Switch - FL SWITCH 2308 - 2702652

### Approvals

EAC



RU C-  
DE.A\*30.B00767