


Inline connector - IB IL SCN-8-CP - 2727608

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Inline connector, colored



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 163020
Weight per Piece (excluding packing)	15.46 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

Dimensions

Height	111.2 mm
Depth	41 mm
Width	12 mm

Connection data

Conductor cross section solid min.	0.08 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section flexible min.	0.08 mm ²
Conductor cross section flexible max.	1.5 mm ²
Conductor cross section AWG min.	28
Conductor cross section AWG max.	16
Stripping length	8 mm

Standards and Regulations

Connection in acc. with standard	CUL
----------------------------------	-----

Inline connector - IB IL SCN-8-CP - 2727608

Classifications

eCl@ss

eCl@ss 4.0	27250281
eCl@ss 4.1	27250281
eCl@ss 5.0	27259205
eCl@ss 5.1	27242692
eCl@ss 6.0	27242692
eCl@ss 7.0	27242692
eCl@ss 8.0	27249290
eCl@ss 9.0	27240692

ETIM

ETIM 2.0	EC000313
ETIM 3.0	EC000313
ETIM 4.0	EC002584
ETIM 5.0	EC002584

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	39121311
UNSPSC 12.01	39121311
UNSPSC 13.2	39121311

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized


Ex Approvals


Approvals submitted

Approval details


Inline connector - IB IL SCN-8-CP - 2727608

Approvals

UL Recognized 	
mm ² /AWG/kcmil	26-16
Nominal current I _N	10 A
Nominal voltage U _N	24 V

cUL Recognized 	
mm ² /AWG/kcmil	26-16
Nominal current I _N	10 A
Nominal voltage U _N	24 V

EAC

cULus Recognized 
--