

## Interface converter - PSM-ME-RS232/RS232-P - 2744461

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Interface converter, for the isolation of RS-232 (V.24) interfaces, 4 channels, rail-mountable

### Product Features

- Mounting on standard EN DIN rails
- In the case of variable cable lengths, the RS-232 connection on the field side can be established conveniently using plug-in screw terminal blocks
- High-quality 3-way isolation up to 2 kV (VCC // RS-232 // RS-232)
- Integrated surge protection with transient discharge to the DIN rail
- Maximum transmission speed of 115.2 kbps
- Transmission of TxD/RxD data channels and RTS/CTS control lines
- 24 V DC or AC power supply suitable for the control cabinet
- Active data transmission indicated by separate data indicators for the transmit and receive channels



### Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	181.2 g
Custom tariff number	85176200
Country of origin	Germany

### Technical data

#### Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

#### Dimensions

Width	22.5 mm
Height	99 mm
Depth	118.6 mm

# Interface converter - PSM-ME-RS232/RS232-P - 2744461

## Technical data

### Ambient conditions

Ambient temperature (operation)	0 °C ... 55 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Altitude	5000 m (For restrictions see manufacturer's declaration)
Degree of protection	IP20
Noise immunity	EN 61000-6-2:2005

### General

Transmission channels	4 (2/2), Rx/D, Tx/D, RTS, CTS; full duplex
Bit delay	< 3 µs
Bit distortion	< 5 %
Electrical isolation	VCC // V.24 (RS-232) (A) // V.24 (RS-232) (B)
Test voltage data interfaces	2 kV AC
Test voltage data interface/power supply	2 kV AC
	2 kV
Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise emission	EN 61000-6-3
Net weight	123.18 g
Housing material	PA
Color	green
MTBF	2263 Years (Telcordia standard, 25°C temperature, 21% operating cycle (5 days a week, 8 hours a day))
	438 Years (Telcordia standard, 40°C temperature, 34.25% operating cycle (5 days a week, 12 hours a day))
Conformance	CE-compliant
UL, USA / Canada	508 recognized
	Class I, Div. 2, Groups A, B, C, D
	Class I, Zone 2, AEx nA IIC T4
	Class I, Zone 2, Ex nA IIC T4 Gc X

### Power supply

Nominal supply voltage	24 V AC/DC ±20 %
Supply voltage range	19.2 V AC/DC ... 28.8 V AC/DC
Typical current consumption	40 mA (24 V DC)

### Serial interface

Interface 1	V.24 (RS-232) interface in acc. with ITU-T V.28, EIA/TIA-232, DIN 66259-1
Connection method	D-SUB-9 plug
Transmission length	15 m (twisted pair)
Conductor cross section flexible min.	0.2 mm²

## Interface converter - PSM-ME-RS232/RS232-P - 2744461

### Technical data

#### Serial interface

Conductor cross section flexible max.	2.5 mm <sup>2</sup>
Conductor cross section AWG min.	24
Conductor cross section AWG max.	13
Serial transmission speed	115.2 kbps
Interface 2	V.24 (RS-232) interface in acc. with ITU-T V.28, EIA/TIA-232, DIN 66259-1
Connection method	Pluggable screw connection
Transmission length	15 m (twisted pair)
Conductor cross section flexible min.	0.2 mm <sup>2</sup>
Conductor cross section AWG min.	24
Conductor cross section AWG max.	13

#### Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise emission	EN 61000-6-3
Noise immunity	EN 61000-6-2:2005
Connection in acc. with standard	CUL
Conformance	CE-compliant
UL, USA / Canada	508 recognized
	Class I, Div. 2, Groups A, B, C, D
	Class I, Zone 2, AEx nA IIC T4
	Class I, Zone 2, Ex nA IIC T4 Gc X

### Classifications

#### eCl@ss

eCl@ss 4.0	27250312
eCl@ss 4.1	27250312
eCl@ss 5.0	27242208
eCl@ss 5.1	27242208
eCl@ss 6.0	27242208
eCl@ss 7.0	27242208
eCl@ss 8.0	27242208

#### ETIM

ETIM 2.0	EC000310
ETIM 3.0	EC000310
ETIM 4.0	EC000310
ETIM 5.0	EC000310

# Interface converter - PSM-ME-RS232/RS232-P - 2744461

## Classifications

### UNSPSC

UNSPSC 6.01	30211506
UNSPSC 7.0901	39121008
UNSPSC 11	39121008
UNSPSC 12.01	39121008
UNSPSC 13.2	43201553

## Approvals

### Approvals

---

#### Approvals

UL Recognized / cUL Recognized / DNV / EAC / cULus Recognized

---

#### Ex Approvals

UL Recognized / cUL Recognized / UL Listed / cUL Listed / cULus Recognized / cULus Listed

---

#### Approvals submitted

---

### Approval details

UL Recognized

cUL Recognized

DNV


EAC

cULus Recognized

# Interface converter - PSM-ME-RS232/RS232-P - 2744461


## Drawings

Application drawing



Electrical isolation

Application drawing



Interface adaptation