

FO converters - FL MC 1000 SC - 2891320

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



FO converter with SC duplex fiber optic connection (1300 nm), for converting 100Base-TX to multi-mode fiberglass. Auto MDI(X) function and comprehensive link diagnostics. DIN rail mountable.

Product Description


The FL MC 1000 SC media converter comes with one 10/100 Mbps twisted-pair RJ45 port and one 100 Mbps multimode fiber port with an SC-duplex connector

Your advantages

- Auto MDI/MDI-X switch-over
- Link fault pass through (LFPT) function for easy connection monitoring
- Data transfer rates of 100 Mbps



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 869614
GTIN	4046356869614
Weight per Piece (excluding packing)	280.000 g
Custom tariff number	85176200
Country of origin	Taiwan

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	28 mm
-------	-------

FO converters - FL MC 1000 SC - 2891320

Technical data

Dimensions

Height	110 mm
Depth	70 mm

Ambient conditions

Ambient temperature (operation)	0 °C ... 60 °C
Ambient temperature (storage/transport)	0 °C ... 70 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)

General

Electrical isolation	VCC // FE // Ethernet
Latency	± 1.3 µs (Store&Forward mode, 10/100 Mbps, depending on the frame size)
Test voltage data interface/power supply	1500 V AC (500 V AC, 1 minute)
Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Mounting position	On horizontal DIN rail NS 35 in acc. with EN 60715
Net weight	278.8 g
Conformance	CE-compliant
UL, USA/Canada	Class I, Div. 2, Groups A, B, C, D

Power supply

Nominal supply voltage	24 V DC
Supply voltage range	12 V DC ... 48 V DC
Typical current consumption	73 mA (24 V DC)
Connection method	Plug-in/screw connection via COMBICON
Conductor cross section flexible max.	2.50 mm ²
Conductor cross section flexible min.	0.20 mm ²
Conductor cross section solid max.	2.50 mm ²
Conductor cross section solid min.	0.20 mm ²
Max. AWG conductor cross section, flexible	12
Min. AWG conductor cross section, flexible	24
Conductor cross section AWG max.	12
Conductor cross section AWG min.	24

Serial interface

Interface 1	Ethernet interface, 100Base-Tx in acc. with IEEE 802.3u
No. of ports	1
Connection method	RJ45 socket, shielded
Transmission medium	Copper
Transmission length	100 m (twisted pair, shielded)
Auto-negotiation modes	Auto

FO converters - FL MC 1000 SC - 2891320

Technical data

Serial interface

Link through	Link fault pass through
MDI-/MDI-X switchover	Auto-MDI(X)
Signal LEDs	LNK/ACT, 100
Serial transmission speed	10/100 Mbps

Optical interface FO

Wavelength	1310 nm
Transmission length incl. 3 dB system reserve	8 km (fiberglass with F-G 62.5/125 0.7 dB/km F1000)
	3.3 km (fiberglass with F-G 62.5/125 2.6 dB/km F600)
	9.6 km (fiberglass with F-G 50/125 0.7 dB/km F1200)
	5.3 km (fiberglass with F-G 50/125 1.6 dB/km F800)
Transmission medium	Multi-mode fiberglass
	GI-HCS fiber
Connection method	SC duplex

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Type of test	Vibration (operation) in acc. with IEC 60068-2-6:1982
Test result	Operation: 5g, 150 Hz, criterion A
Type of test	Shock in acc. with IEC 60068-2-27:1997
Test result	30g, 11 ms period, half-sine shock pulse
Conformance	CE-compliant
UL, USA/Canada	Class I, Div. 2, Groups A, B, C, D

Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 10;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 5.1	27230200
eCl@ss 6.0	27143100
eCl@ss 7.0	27143136
eCl@ss 8.0	19179290
eCl@ss 9.0	19170114

FO converters - FL MC 1000 SC - 2891320

Classifications

ETIM

ETIM 4.0	EC001099
ETIM 5.0	EC001467
ETIM 6.0	EC001099
ETIM 7.0	EC001099

UNSPSC

UNSPSC 13.2	43201549
-------------	----------

Approvals

Approvals

Approvals

UL Listed / cUL Listed / cULus Listed

Ex Approvals

UL Listed / cUL Listed / cULus Listed

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm	FILE E 140324
-----------	--	---	---------------

cUL Listed		http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm	FILE E 140324
------------	--	---	---------------

cULus Listed			
--------------	--	--	--

Accessories

Accessories

Patch cable

FO converters - FL MC 1000 SC - 2891320

Accessories

Patch cable - FL CAT5 PATCH 0,3 - 2832250



Patch cable, CAT5, assembled, 0.3 m

Patch cable - FL CAT5 PATCH 0,5 - 2832263



Patch cable, CAT5, assembled, 0.5 m

Patch cable - FL CAT5 PATCH 1,0 - 2832276



Patch cable, CAT5, assembled, 1 m

Patch cable - FL CAT5 PATCH 1,5 - 2832221



Patch cable, CAT5, assembled, 1.5 m

Patch cable - FL CAT5 PATCH 2,0 - 2832289



Patch cable, CAT5, assembled, 2 m

FO converters - FL MC 1000 SC - 2891320

Accessories

Patch cable - FL CAT5 PATCH 3,0 - 2832292



Patch cable, CAT5, assembled, 3 m

Patch cable - FL CAT5 PATCH 5,0 - 2832580



Patch cable, CAT5, assembled, 5 m

Patch cable - FL CAT5 PATCH 7,5 - 2832616



Patch cable, CAT5, assembled, 7.5 m

Patch cable - FL CAT5 PATCH 10,0 - 2832629



Patch cable, CAT5, assembled, 10 m

Safety locking

Port Guard Security Element - FL PATCH GUARD - 2891424



Lockable security element

FO converters - FL MC 1000 SC - 2891320

Accessories

Key - FL PATCH GUARD KEY - 2891521



Key for lockable security element