

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Knife disconnect terminal block, With test socket screws for insertion of test plugs, Connection type: Screw connection, Cross section: 0.2 mm² - 6 mm², AWG: 24 - 10, Nominal current: 16 A, Nominal voltage: 630 V, Length: 63.5 mm, Width: 6.2 mm, Color: gray, Assembly: NS 35/7,5, NS 35/15, NS 32

Product Features

- Closed housing of double-level terminal blocks
- Space-saving design just 6.2 mm wide
- User-friendly disconnect knife operation



Key Commercial Data

Packing unit	1 pc	
GTIN	4 017918 068516	
Weight per Piece (excluding packing)	16.48 g	
Custom tariff number	85369010	
Country of origin	China	

Technical data

General

Number of levels	1
Number of connections	4
Nominal cross section	4 mm²
Color	gray
Insulating material	PA
Flammability rating according to UL 94	V2
Rated surge voltage	8 kV
Degree of pollution	3
Overvoltage category	III



Technical data

General

Insulating material group	I	
Connection in acc. with standard	IEC 60947-7-1	
Nominal current I _N	16 A	
Maximum load current	16 A (with 6 mm² conductor cross section)	
Nominal voltage U _N	630 V	
Open side panel	Yes	
Shock protection test specification	DIN EN 50274 (VDE 0660-514):2002-11	
Back of the hand protection	guaranteed	
Finger protection	guaranteed	
Result of surge voltage test	Test passed	
Surge voltage test setpoint	9.8 kV	
Result of power-frequency withstand voltage test	Test passed	
Power frequency withstand voltage setpoint	3 kV	
Result of the test for mechanical stability of terminal points (5 x conductor connection)	Test passed	
Result of bending test	Test passed	
Bending test rotation speed	10 rpm	
Bending test turns	135	
Bending test conductor cross section/weight	0.2 mm² / 0.2 kg	
	4 mm² / 0.9 kg	
	6 mm²/ 1.4 kg	
Tensile test result	Test passed	
Conductor cross section tensile test	0.2 mm²	
Tractive force setpoint	10 N	
Conductor cross section tensile test	4 mm ²	
Tractive force setpoint	60 N	
Conductor cross section tensile test	6 mm ²	
Tractive force setpoint	80 N	
Result of tight fit on support	Test passed	
Tight fit on carrier	NS 32/NS 35	
Setpoint	1 N	
Result of voltage-drop test	Test passed	
Result of temperature-rise test	Test passed	
Short circuit stability result	Test performed	
Conductor cross section short circuit testing	4 mm²	
Short-time current	0.18 kA	
Result of thermal test	Test passed	



Technical data

General

Proof of thermal characteristics (needle flame) effective duration	30 s
Relative insulation material temperature index (Elec., UL 746 B)	125 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	125 °C

Dimensions

Width	6.2 mm
Length	63.5 mm
Height NS 35/7,5	47 mm
Height NS 35/15	54.5 mm
Height NS 32	52 mm

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	6 mm ²
Conductor cross section flexible min.	0.2 mm²
Conductor cross section flexible max.	4 mm²
Conductor cross section AWG min.	24
Conductor cross section AWG max.	10
Conductor cross section flexible, with ferrule without plastic sleeve min.	0.25 mm²
Conductor cross section flexible, with ferrule without plastic sleeve max.	4 mm²
Conductor cross section flexible, with ferrule with plastic sleeve min.	0.25 mm²
Conductor cross section flexible, with ferrule with plastic sleeve max.	1.5 mm²
2 conductors with same cross section, solid min.	0.2 mm²
2 conductors with same cross section, solid max.	1 mm ²
2 conductors with same cross section, stranded min.	0.2 mm²
2 conductors with same cross section, stranded max.	1.5 mm²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1 mm²
Cross section with insertion bridge, solid max.	2.5 mm²
Cross section with insertion bridge, stranded max.	2.5 mm²
Connection method	Screw connection
Stripping length	8 mm
Internal cylindrical gage	A4
Screw thread	M3



Technical data

Connection data

Tightening torque, min	0.6 Nm
Tightening torque max	0.8 Nm

Standards and Regulations

Connection in acc. with standard	CSA	
	IEC 60947-7-1	
Flammability rating according to UL 94	V2	

Classifications

eCl@ss

eCl@ss 4.0	27141126
eCl@ss 4.1	27141126
eCl@ss 5.0	27141126
eCl@ss 5.1	27141126
eCl@ss 6.0	27141126
eCl@ss 7.0	27141126
eCl@ss 8.0	27141126
eCl@ss 9.0	27141126

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000902
ETIM 5.0	EC000902

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

Approvals



Approvals

PRS

Approvals			
CSA / UL Recognized / cUL Re	CSA / UL Recognized / cUL Recognized / RS / PRS / EAC / EAC / cULus Recognized		
Ex Approvals			
Approvals submitted			
Approval details			
CSA ①			
	В	С	D
mm²/AWG/kcmil	22-10	22-10	22-10
Nominal current IN	15 A	15 A	10 A
Nominal voltage UN	300 V	300 V	600 V
UL Recognized \$\)			
mm²/AWG/kcmil		30-10	
Nominal current IN		15 A	
Nominal voltage UN 600 V			
cUL Recognized			
mm²/AWG/kcmil	72/AM/C/komil		
Nominal current IN			
Nominal voltage UN 600 V			
RS			



Approvals

EAC	
EAC	
cULus Recognized C S Us	

Drawings

Circuit diagram

ما لم

Phoenix Contact 2016 © - all rights reserved http://www.phoenixcontact.com