

UFBK 2/2- 24DC-BE

This product has been replaced by a newer version.

Order No.: 2792918

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2792918>

Base element with universal foot for mounting on NS 32 or NS 35/7.5,
housing width: 17.5 mm, nominal voltage: 24 V DC

Commercial data

EAN	4017918072704
Pack	10 pcs.
Customs tariff	85363010
Weight/Piece	0.07355 KG

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Product description

Base element to accept the protective plug UFBK 2/2-24 DC-ST.

Technical data

General

Stripping length	8 mm
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Nominal current I _N	2 A
Ambient temperature (operation)	-40 °C ... 60 °C
Housing material	PA
Inflammability class acc. to UL 94	V2

Degree of protection	IP20
Pitch unit	1 Div.

Certificates / Approvals



Certification BZT, CSA

CSA

Nominal voltage U_N	24 V
Nominal current I_N	2 A

Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2009 Phoenix Contact
Technical modifications reserved;