

## Wiring bridge - MPB 18/1- 7 BU - 2856278

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Wiring bridge for modules with connecting pitch 17.5 mm, 1-phase, 7-pos., color: Blue

### Your advantages

- In combination with other devices in the distribution board, such as residual current devices and miniature circuit breakers
- Practical wiring of all common applications
- For combinations of lightning and surge arresters
- End covers are used to terminate and insulate individually cut bridges

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 727437
GTIN	4017918727437
Weight per Piece (excluding packing)	34.300 g
Custom tariff number	85369095
Country of origin	Germany

### Technical data

#### Dimensions

Height	126.4 mm
--------	----------

#### General

Nominal current $I_N$	100 A
Number of positions	7

# Wiring bridge - MPB 18/1- 7 BU - 2856278

## Technical data

### General

Color	blue
Housing material	Plastic
Type	Comb bridge

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 4.0	27140200
eCl@ss 4.1	27140200
eCl@ss 5.0	27140200
eCl@ss 5.1	27140200
eCl@ss 6.0	27371300
eCl@ss 7.0	27371306
eCl@ss 8.0	27371306
eCl@ss 9.0	27371306

### ETIM

ETIM 2.0	EC000489
ETIM 3.0	EC000489
ETIM 4.0	EC000489
ETIM 5.0	EC000215
ETIM 6.0	EC000215
ETIM 7.0	EC000215

### UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620

## Approvals

### Approvals

## Wiring bridge - MPB 18/1- 7 BU - 2856278

### Approvals

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		RU C- DE.A*30.B.01742
-----	---	--------------------------

---