

Signal conditioner - MINI MCR-SL-U-UI-NC - 2865007

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



MCR 3-way isolation amplifier, with configurable input/output, for electrical isolation and conversion of analog signals up to 30 V, with screw connection, standard configuration

Product Description

The 6.2 mm wide configurable 3-way isolating amplifier MINI MCR-SL-U-UI-... is used for electrical isolation, conversion, amplification and filtering of standard signals.

The signals 0...24 V and 0...30 V can be processed on the input side.

The analog signals 0...20 mA, 4...20 mA, 0...10 V, 2...10 V, 0...5 V or 1..5 V are available electrically isolated on the output side.

The DIP switches, which can be accessed on the side of the housing, can be used to configure the input and output signal ranges.

Power (19.2 V DC to 30 V DC) can be supplied through connection terminal blocks on the modules or in conjunction with the DIN rail connector.

Product Features

- Power supply possible via the foot element (TBUS)
- Low power consumption
- Highly-compact isolating amplifier for electrical isolation, conversion, amplification, and filtering of 24 V or
- 30 V DC signals to create standard analog signals
- Up to 12 signal combinations can be configured using DIP switches
- 3-way isolation



Key Commercial Data

| | |
|--------------------------------------|----------|
| Packing unit | 1 pc |
| Weight per Piece (excluding packing) | 72.4 g |
| Custom tariff number | 85437090 |
| Country of origin | Germany |

Technical data

Note

Signal conditioner - MINI MCR-SL-U-UI-NC - 2865007

Technical data

Note

| | |
|-------------------------|---|
| Utilization restriction | EMC: class A product, see manufacturer's declaration in the download area |
|-------------------------|---|

Dimensions

| | |
|--------|----------|
| Width | 6.2 mm |
| Height | 93.1 mm |
| Depth | 102.5 mm |

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 65 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Degree of protection | IP20 |

Input data

| | |
|-----------------------------------|-----------------------------|
| Number of inputs | 1 |
| Configurable/programmable | Yes, unconfigured |
| Voltage input signal | 0 V ... 24 V |
| | 0 V ... 30 V |
| Max. input voltage | 50 V DC |
| Input resistance of voltage input | approx. 125 kΩ (0 ... 24 V) |
| | approx. 155 kΩ (0 ... 30 V) |

Output data

| | |
|---------------------------------|--------------------|
| Number of outputs | 1 |
| Configurable/programmable | Yes, unconfigured |
| Voltage output signal | 0 V ... 10 V |
| | 0 V ... 5 V |
| | 1 V ... 5 V |
| | 2 V ... 10 V |
| Current output signal | 0 mA ... 20 mA |
| | 4 mA ... 20 mA |
| Max. output voltage | ≤ 12.5 V |
| Max. output current | 28 mA |
| Short-circuit current | ≤ 22 mA |
| Load/output load voltage output | > 10 kΩ |
| Load/output load current output | < 500 Ω (at 20 mA) |

Power supply

| | |
|------------------------|---------|
| Nominal supply voltage | 24 V DC |
|------------------------|---------|

Signal conditioner - MINI MCR-SL-U-UI-NC - 2865007

Technical data

Power supply

| | |
|--------------------------|---|
| Supply voltage range | 19.2 V DC ... 30 V DC (The DIN rail bus connector (ME 6,2 TBUS-2 1,5/5-ST-3,81 GN, Order No. 2869728) can be used to bridge the supply voltage. It can be snapped onto a 35 mm DIN rail according to EN 60715)) |
| Max. current consumption | < 19 mA (at 24 V DC incl. load) |
| Power consumption | < 450 mW |

Connection data

| | |
|---------------------------------------|---------------------|
| Connection method | Screw connection |
| Conductor cross section solid min. | 0.2 mm ² |
| Conductor cross section solid max. | 2.5 mm ² |
| Conductor cross section AWG min. | 26 |
| Conductor cross section AWG max. | 12 |
| Conductor cross section flexible min. | 0.2 mm ² |
| Conductor cross section flexible max. | 2.5 mm ² |
| Stripping length | 12 mm |
| Screw thread | M3 |

General

| | |
|-----------------------------------|---|
| No. of channels | 1 |
| Maximum transmission error | < 0.1 % (of final value) |
| | < 0.4 % (Without adjustment) |
| Maximum temperature coefficient | < 0.01 %/K |
| Temperature coefficient, typical | < 0.002 %/K |
| Limit frequency (3 dB) | approx. 100 Hz |
| Step response (10-90%) | approx. 3.5 ms |
| Protective circuit | Transient protection |
| Electrical isolation | Basic insulation according to EN 61010 |
| Overvoltage category | II |
| Degree of pollution | 2 |
| Rated insulation voltage | 50 V AC/DC |
| Test voltage, input/output/supply | 1.5 kV (50 Hz, 1 min.) |
| Electromagnetic compatibility | Conformance with EMC directive |
| Noise emission | EN 61000-6-4 |
| Noise immunity | EN 61000-6-2 When being exposed to interference, there may be minimal deviations. |
| Color | green |
| Housing material | PBT |
| Mounting position | any |

Signal conditioner - MINI MCR-SL-U-UI-NC - 2865007

Technical data

General

| | |
|-----------------------|--|
| Assembly instructions | To bridge the supply voltage, the DIN rail connector (ME 6,2 TBUS-2 1,5/5-ST-3,81 GN, Order No. 2869728) can be used. It can be snapped onto a 35 mm DIN rail according to EN 60715. |
| Conformance | CE-compliant |
| ATEX | # II 3 G Ex nA IIC T4 Gc X |
| UL, USA / Canada | UL 508 Recognized |
| | Class I, Div. 2, Groups A, B, C, D T5 |
| GL | GL EMC 2 D |

EMC data

| | |
|--|--------------------------|
| Designation | Electromagnetic RF field |
| Standards/regulations | EN 61000-4-3 |
| Typical deviation from the measuring range final value | 5 % |
| Designation | Fast transients (burst) |
| Standards/regulations | EN 61000-4-4 |
| Typical deviation from the measuring range final value | 5 % |
| Designation | Conducted interferences |
| Standards/regulations | EN 61000-4-6 |
| Typical deviation from the measuring range final value | 5 % |

Standards and Regulations

| | |
|----------------------------------|--|
| Electromagnetic compatibility | Conformance with EMC directive |
| Noise emission | EN 61000-6-4 |
| Connection in acc. with standard | CUL |
| Standards/regulations | EN 61000-4-2 |
| Designation | Electromagnetic RF field |
| Standards/regulations | EN 61000-4-3 |
| | EN 61000-4-4 |
| | EN 61000-4-5 |
| Designation | Conducted interferences |
| Standards/regulations | EN 61000-4-6 |
| Electrical isolation | Basic insulation according to EN 61010 |
| Conformance | CE-compliant |
| ATEX | # II 3 G Ex nA IIC T4 Gc X |
| UL, USA / Canada | UL 508 Recognized |
| | Class I, Div. 2, Groups A, B, C, D T5 |
| GL | GL EMC 2 D |

Signal conditioner - MINI MCR-SL-U-UI-NC - 2865007

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27210120 |
| eCl@ss 4.1 | 27210120 |
| eCl@ss 5.0 | 27210120 |
| eCl@ss 5.1 | 27210120 |
| eCl@ss 6.0 | 27210120 |
| eCl@ss 7.0 | 27210120 |
| eCl@ss 8.0 | 27210120 |
| eCl@ss 9.0 | 27210120 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC001485 |
| ETIM 3.0 | EC001485 |
| ETIM 4.0 | EC001485 |
| ETIM 5.0 | EC002653 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211506 |
| UNSPSC 7.0901 | 39121008 |
| UNSPSC 11 | 39121008 |
| UNSPSC 12.01 | 39121008 |
| UNSPSC 13.2 | 39121008 |

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / GL / EAC / cULus Recognized

Ex Approvals

UL Listed / cUL Listed / ATEX / cULus Listed

Approvals submitted

Approval details

Signal conditioner - MINI MCR-SL-U-UI-NC - 2865007

Approvals

UL Recognized

cUL Recognized


GL

EAC


cULus Recognized

Drawings

Application drawing



Block diagram



Signal conversion to uninterruptible power supply (UPS)

Signal conditioner - MINI MCR-SL-U-UI-NC - 2865007

Dimensional drawing

