

Passive module - VIP-2/SC/FLK16/ISP 4AI 2DMU - 2903869

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOFACE Professional (VIP) module for Siemens ET200 ISP controllers. Interface to HART analog input, 4 channel. 125 V AC/DC, 1 A rating, 2 wire.

Your advantages

- ✓ Interface from field devices to HART® analog input 6ES7134-7TD00-0AB0 card
- ✓ I/O marking for field wiring clearly identified when device is mounted
- ✓ Compact design reduces space requirements in the control cabinet
- ✓ A single, metal mounting foot allows easy installation and removal to the mounting rail



Key Commercial Data

| | |
|--------------------------------------|---------------|
| Packing unit | 1 pc |
| GTIN | |
| GTIN | 4046356827546 |
| Weight per Piece (excluding packing) | 100.000 g |
| Custom tariff number | 85366990 |
| Country of origin | United States |

Technical data

Dimensions

| | |
|--------|---------|
| Width | 45 mm |
| Height | 65.5 mm |
| Depth | 56 mm |

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
|---------------------------------|------------------|

Passive module - VIP-2/SC/FLK16/ISP 4AI 2DMU - 2903869

Technical data

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
|---|------------------|

General

| | |
|---------------------------------|------------|
| Nominal voltage U_N | 60 V AC/DC |
| Max. perm. current (per branch) | 1 A |
| Number of positions | 16 |
| Status display | No |

Connection data

| | |
|----------------------------------|---|
| Connection name | Field level |
| Connection in acc. with standard | IEC / EN |
| Connection method | Screw connection |
| Stripping length | 8 mm |
| Screw thread | M 3 |
| Conductor cross section solid | 0.2 mm ² ... 4 mm ² |
| Conductor cross section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross section AWG | 24 ... 12 |

Connection data 2

| | |
|-----------------------|-------------------|
| Connection name | Controller level |
| Connection method | IDC/FLK pin strip |
| Number of connections | 1 |
| Number of positions | 16 |
| Pitch | 2.54 mm |

Supported controller

| | |
|---------------------|--------------------|
| Controller | Siemens ET200 ISP |
| - suitable I/O card | 6ES7134-7TD00-0AB0 |

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|


Environmental Product Compliance

| | |
|------------|---|
| REACH SVHC | Lead 7439-92-1 |
| China RoHS | Environmentally Friendly Use Period = 50 years |
| | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

Drawings

Passive module - VIP-2/SC/FLK16/ISP 4AI 2DMU - 2903869

Circuit diagram



Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27250300 |
| eCl@ss 4.1 | 27250300 |
| eCl@ss 5.0 | 27250300 |
| eCl@ss 5.1 | 27250300 |
| eCl@ss 6.0 | 27242600 |
| eCl@ss 7.0 | 27141152 |
| eCl@ss 8.0 | 27141152 |
| eCl@ss 9.0 | 27141152 |

ETIM

| | |
|----------|----------|
| ETIM 4.0 | EC002780 |
| ETIM 5.0 | EC002780 |
| ETIM 6.0 | EC002780 |
| ETIM 7.0 | EC002780 |

Passive module - VIP-2/SC/FLK16/ISP 4AI 2DMU - 2903869

Classifications

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211824 |
| UNSPSC 7.0901 | 39121421 |
| UNSPSC 11 | 39121421 |
| UNSPSC 12.01 | 39121421 |
| UNSPSC 13.2 | 39121432 |
| UNSPSC 18.0 | 39121432 |
| UNSPSC 19.0 | 39121432 |
| UNSPSC 20.0 | 39121432 |
| UNSPSC 21.0 | 39121432 |

Approvals


Approvals


Approvals

CSA / UL Recognized / cUL Recognized / cULus Recognized

Ex Approvals

Approval details

| | | | |
|----------------------------|---|---|---------|
| CSA |  | http://www.csagroup.org/services-industries/product-listing/ | 2122203 |
| Nominal voltage UN | | 125 V | |
| Nominal current IN | | 1 A | |
| mm ² /AWG/kcmil | | 30-12 | |

| | | | |
|----------------------------|---|---|---------------|
| UL Recognized |  | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | FILE E 238705 |
| Nominal voltage UN | | 125 V | |
| Nominal current IN | | 1 A | |
| mm ² /AWG/kcmil | | 30-12 | |

Passive module - VIP-2/SC/FLK16/ISP 4AI 2DMU - 2903869

Approvals

| | | | |
|----------------------------|--|---|---------------|
| cUL Recognized | | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | FILE E 238705 |
| Nominal voltage UN | | 125 V | |
| Nominal current IN | | 1 A | |
| mm ² /AWG/kcmil | | 30-12 | |

| | |
|------------------|--|
| cULus Recognized | |
|------------------|--|

Accessories

Accessories

System cable

Cable - VIP-CAB-FLK16/0,14/0,5M - 2318460



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position, 180 °-Out put); connection 2: IDC/FLK socket strip (1x 16-position, 90 °-out put); cable length: 0.5 m

Cable - VIP-CAB-FLK16/0,14/1,0M - 2318473



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position, 180 °-Out put); connection 2: IDC/FLK socket strip (1x 16-position, 90 °-out put); cable length: 1 m

Cable - VIP-CAB-FLK16/0,14/1,5M - 2318486



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position, 180 °-Out put); connection 2: IDC/FLK socket strip (1x 16-position, 90 °-out put); cable length: 1.5 m

Passive module - VIP-2/SC/FLK16/ISP 4AI 2DMU - 2903869

Accessories

Cable - VIP-CAB-FLK16/0,14/2,0M - 2318499



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position, 180 °-Out put); connection 2: IDC/FLK socket strip (1x 16-position, 90 °-out put); cable length: 2 m

Cable - VIP-CAB-FLK16/0,14/3,0M - 2318509



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position, 180 °-Out put); connection 2: IDC/FLK socket strip (1x 16-position, 90 °-out put); cable length: 3 m

Cable - VIP-CAB-FLK16/0,14/4,0M - 2318512



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position, 180 °-Out put); connection 2: IDC/FLK socket strip (1x 16-position, 90 °-out put); cable length: 4 m

Cable - VIP-CAB-FLK16/0,14/6,0M - 2318525



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position, 180 °-Out put); connection 2: IDC/FLK socket strip (1x 16-position, 90 °-out put); cable length: 6 m

Cable - VIP-CAB-FLK16-0,14/... - 2318538



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position, 180 °-Out put); connection 2: IDC/FLK socket strip (1x 16-position, 90 °-out put); cable length: variable

Passive module - VIP-2/SC/FLK16/ISP 4AI 2DMU - 2903869

Accessories

Cable - FLK 16/EZ-DR/ 50/KONFEK - 2299291



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position); cable length: 0.5 m

Cable - FLK 16/EZ-DR/ 100/KONFEK - 2299301



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position); cable length: 1 m

Cable - FLK 16/EZ-DR/ 150/KONFEK - 2299314



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position); cable length: 1.5 m

Cable - FLK 16/EZ-DR/ 200/KONFEK - 2299327



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position); cable length: 2 m

Cable - FLK 16/EZ-DR/ 300/KONFEK - 2299330



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position); cable length: 3 m

Passive module - VIP-2/SC/FLK16/ISP 4AI 2DMU - 2903869

Accessories

Cable - FLK 16/EZ-DR/ 400/KONFEK - 2299343



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position); cable length: 4 m

Cable - FLK 16/EZ-DR/ 600/KONFEK - 2299356



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position); cable length: 6 m

Cable - FLK 16/EZ-DR/ 800/KONFEK - 2299369



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position); cable length: 8 m

Cable - FLK 16/EZ-DR/1000/KONFEK - 2299372



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position); cable length: 10 m

Cable - FLK EZ-DR.../.../... - 2295059



Round cable, with preassembly, not shielded, variable cable length

Passive module - VIP-2/SC/FLK16/ISP 4AI 2DMU - 2903869

Accessories

Cable - FLK 16/EZ-DR/ 100/KONFEK/S - 2304542



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position) (The braided shield is routed to a separate cable end.); cable length: 1 m

Cable - FLK 16/EZ-DR/ 150/KONFEK/S - 2304623



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position) (The braided shield is routed to a separate cable end.); cable length: 1.5 m

Cable - FLK 16/EZ-DR/ 200/KONFEK/S - 2304555



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position) (The braided shield is routed to a separate cable end.); cable length: 2 m

Cable - FLK 16/EZ-DR/ 300/KONFEK/S - 2318088



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position) (The braided shield is routed to a separate cable end.); cable length: 3 m

Cable - FLK 16/EZ-DR/ 400/KONFEK/S - 2318091



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position) (The braided shield is routed to a separate cable end.); cable length: 4 m

Passive module - VIP-2/SC/FLK16/ISP 4AI 2DMU - 2903869

Accessories

Cable - FLK 16/EZ-DR/ 500/KONFEK/S - 2318965



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position) (The braided shield is routed to a separate cable end.); cable length: 5 m

Cable - FLK 16/EZ-DR/ 600/KONFEK/S - 2314477



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position) (The braided shield is routed to a separate cable end.); cable length: 6 m

Cable - FLK EZ-DR-S.../.../... - 2295046



Round cable, with preassembly, shielded, variable cable length

Terminal marking

Marker for terminal blocks - UC-TM 4 - 0818111



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snap into tall marker groove, for terminal block width: 4.2 mm, lettering field size: 3.6 x 10.5 mm, Number of individual labels: 120

Marker for terminal blocks - UC-TM 6 - 0818085



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snap into tall marker groove, for terminal block width: 6.2 mm, lettering field size: 5.6 x 10.5 mm, Number of individual labels: 80

Passive module - VIP-2/SC/FLK16/ISP 4AI 2DMU - 2903869

Accessories

Marker for terminal blocks - UCT-TM 6 - 0828736



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snap into tall marker groove, for terminal block width: 6.2 mm, lettering field size: 5.6 x 10.5 mm, Number of individual labels: 60

Zack marker strip - ZB 5,08:UNBEDRUCKT - 0809793



Zack marker strip, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snap into tall marker groove, for terminal block width: 5.08 mm, lettering field size: 4.98 x 10.5 mm, Number of individual labels: 10

Zack marker strip - ZB 22:UNBEDRUCKT - 0811862



Zack marker strip, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snap into tall marker groove, for terminal block width: 22 mm, lettering field size: 10.5 x 21.8 mm, Number of individual labels: 4