

Antenna cable - RAD-CAB-RG213-40 - 2867377

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Antenna cable, outside diameter: 10 mm (0.4 in.), inner conductor: solid, attenuation: 2.9 dB at 900 MHz, connection: 2 x N (male), cable length: 12 m (40 ft.)




Your advantages

- UV resistant
- For outdoor installation



Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 931735
GTIN	4017918931735
Weight per Piece (excluding packing)	1,987.000 g
Custom tariff number	85442000
Country of origin	United States

Technical data

Dimensions

Fixed cable length	12 m
External diameter	10.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

General

Connection 1	Connector connection
--------------	----------------------

Antenna cable - RAD-CAB-RG213-40 - 2867377

Technical data

General

Connection method	Type N (male)
Note	Both sides
Cable type	RG-213U
Outer sheath, material	PE
External sheath, color	black
Minimum bending radius	127.00 mm
Frequency range	0.1 GHz ... 1 GHz
Impedance	50 Ω

Attenuation

868 / 900 MHz	2.88 dB
---------------	---------

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	27060805
eCl@ss 4.1	27060805
eCl@ss 5.0	27061805
eCl@ss 5.1	27061800
eCl@ss 6.0	27061800
eCl@ss 7.0	27061805
eCl@ss 8.0	27060310
eCl@ss 9.0	27060310

ETIM

ETIM 2.0	EC000019
ETIM 3.0	EC000019
ETIM 4.0	EC000019
ETIM 5.0	EC001682
ETIM 6.0	EC001682
ETIM 7.0	EC001682

UNSPSC

UNSPSC 6.01	26121608
-------------	----------

Antenna cable - RAD-CAB-RG213-40 - 2867377

Classifications

UNSPSC

UNSPSC 7.0901	26121608
UNSPSC 11	26121608
UNSPSC 12.01	26121608
UNSPSC 13.2	26121606