

Surge protection device - TTC-6-2XTVSD-24DC-PT - 2906808

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Fine surge protection with integrated status indicator for two signal wires with common reference potential.

Why buy this product

- ✓ Space-saving installation due to the narrow overall width of 6.2 mm
- ✓ Quick and tool-free installation of surge protective devices, thanks to Push-in connection technology



Key Commercial Data

Packing unit	1
GTIN	 4 055626 135724
GTIN	4055626135724
Custom tariff number	85363010

Technical data

Dimensions

Height	105.8 mm
	105.8 mm
Width	6.2 mm
Depth	69.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Degree of protection	IP20

Surge protection device - TTC-6-2XTVSD-24DC-PT - 2906808

Technical data

General

Housing material	PBT
Flammability rating according to UL 94	V-0
Color	traffic grey A RAL 7042
Mounting type	DIN rail: 35 mm
Design	Rail-mountable module, one-piece
Direction of action	Line-Earth Ground

Protective circuit

IEC test classification	C1
	C3
Nominal voltage U_N	24 V DC
Maximum continuous voltage U_C	30 V DC
Rated current	6 A (55 °C)
Residual current I_{PE}	$\leq 10 \mu A$
Nominal discharge current I_n (8/20) μs (core-earth)	0.5 kA
Total discharge current I_{total} (8/20) μs	1 kA
Voltage protection level U_p (core-ground)	$\leq 60 V$ (C1 - 1 kV/500 A)
	$\leq 45 V$ (C3 - 25 A)
	$\leq 50 V$ (C3 - 100 A)
Response time t_A (core-earth)	$\leq 1 ns$
Input attenuation aE, asym.	typ. 0.3 dB ($\leq 300 kHz / 150 \Omega$)
Cut-off frequency f_g (3 dB), asym. (PE) in 150 Ohm system	typ. 960 kHz
Capacity (core-earth)	typ. 2.2 nF
Resistance in series	$\leq 100 m\Omega$
Surge protection fault message	None
Max. required back-up fuse	6.3 A (FF)
Impulse durability (conductor-ground)	C1 - 1 kV/500 A
	C3 - 100 A

Connection data

Connection method	Push-in connection
Connection method IN	Push-in connection
Connection method OUT	Push-in connection
Stripping length	8 mm
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section solid	0.2 mm ² ... 4 mm ²
Conductor cross section AWG	24 ... 12

Standards and Regulations

Surge protection device - TTC-6-2XTVSD-24DC-PT - 2906808


Technical data

Standards and Regulations


Standards/specifications	IEC 61643-21 2000 + corrigendum 2001 + A1:2008, modified + A2:2012
	EN 61643-21 2001 + A1:2009 + A2:2013

Drawings


Diagram



Dimensional drawing



Circuit diagram



Approvals

Approvals

Approvals

UL Listed

Ex Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 138168
-----------	--	-------------------------------------------------------------------------------------------------------------------------------------------------------	---------------

