

Timer relay - PLC-TR-1T-MUL-300M - 2910140


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Ultra-narrow multi-function time relay with 4 functions, adjustable time range (0.1 s - 300 min), 1 PDT, screw connection



Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 430492
GTIN	4055626430492
Weight per Piece (excluding packing)	60.000 g
Custom tariff number	85364900
Country of origin	Germany

Technical data

Dimensions

Width	6.2 mm
Height	80 mm
Depth	86 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 65 °C
Ambient temperature (storage/transport)	-25 °C ... 80 °C
Maximum altitude	≤ 2000 m
Permissible humidity (operation)	15 % ... 85 %
Degree of protection	IP20
Noise immunity	EN 61000-6-2

Timer relay - PLC-TR-1T-MUL-300M - 2910140

Technical data

Coil side

Input voltage range	24 V DC (19.2 V DC ... 30 V DC)
Function	E: With switch-on delay
	Es: With switch-on delay and control contact
	Rs: With release delay and control contact
	Bi: Flashing beginning with pulse
Setting range time	0.1 s ... 300 min. (4 time end ranges)
Recovery time	50 ms

Contact side

Contact type	1 floating PDT
Maximum switching voltage	250 V AC
Interrupting rating (ohmic load) max.	1500 VA (6 A / 250 V AC)
Output fuse	6.3 A (fast-blow)

General

Status display	Green LED (POWER)
	Yellow LED (relay active)
Mechanical service life	approx. 2×10^7 cycles
Nominal power consumption	0.45 W (at 24 V DC)
Mounting position	any
Assembly instructions	on standard DIN rail NS 35 in accordance with EN 60715
Color	traffic grey A RAL 7042
Housing insulation material	Polyamide PA, self-extinguishing
Permissible humidity (operation)	15 % ... 85 %

Connection data

Connection method	Screw connection
Stripping length	8 mm
Conductor cross section solid	0.14 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross section AWG	30 ... 12
Torque	0.6 Nm ... 0.8 Nm ()
	5 lb _f -in. ... 7 lb _f -in.

Control contact

Connection name	Non-floating, terminals A1-B1
Control pulse length	≥ 50 ms

Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
-------------------------------	---

Timer relay - PLC-TR-1T-MUL-300M - 2910140

Technical data

Standards and Regulations

Noise emission	EN 61000-6-3
Noise immunity	EN 61000-6-2
Standards/regulations	IEC 61812-1
	IEC 60947-5-1
Rated insulation voltage	300 V AC
Rated surge voltage	6 kV
Insulation	Basic insulation
Pollution degree	2
Overvoltage category	III
Low Voltage Directive	Conformance with Low Voltage Directive 2014/35/EU

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	27371605
eCl@ss 11.0	27371605
eCl@ss 8.0	27371605
eCl@ss 9.0	27371605

ETIM

ETIM 5.0	EC001439
ETIM 6.0	EC001439
ETIM 7.0	EC001439

Approvals

Approvals

Approvals



UL Listed / cUL Listed / cULus Listed

Timer relay - PLC-TR-1T-MUL-300M - 2910140

Approvals

Ex Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 172140
cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 172140
cULus Listed	