

Industrial Ethernet Switch - FL SWITCH 4824E-4GC - 2891072

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Rack-mount managed Ethernet switch meets IEC 61850-3 and IEEE 1613. Provides 24 RJ45 ports at 10/100 Mbps and four gigabit combo ports (10/100/1000 Mbps RJ45 connection; 1000 Mbps fiber optic connection requires 1000 Mbps SFP module)



Why buy this product

- Network structure according to IEC 61850
- IEEE 1613

Ethernet IEC 61850-3

Key Commercial Data

Packing unit	1 STK
Weight per Piece (excluding packing)	1.000 g
Custom tariff number	85176200
Country of origin	Taiwan

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	442 mm
Height	44 mm
Depth	375 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Air pressure (operation)	57 kPa ... 108 kPa (up to 4850 m above mean sea level)

Industrial Ethernet Switch - FL SWITCH 4824E-4GC - 2891072

Technical data

Ambient conditions

Air pressure (storage/transport)	57 kPa ... 108 kPa (up to 4850 m above mean sea level)
----------------------------------	--

Interfaces

Interface 1	Ethernet (RJ45)
No. of ports	24 (RJ45 ports)
Connection method	RJ45
Note on connection method	Auto negotiation and autocrossing
Transmission physics	Ethernet in RJ45 twisted pair
Transmission speed	10/100 Mbps
Transmission length	100 m
Interface 3	Ethernet (RJ45/FO combo)
No. of ports	4
Connection method	Combo
Note on connection method	Auto negotiation and autocrossing (RJ45 interface)
Transmission physics	Ethernet RJ45 (10/100/1000 Mbps) or SFP (1000 Mbps)
Transmission speed	10/100/1000 Mbps

Function

Basic functions	Store and forward switch, Extended Ring and IEEE redundancy, Multicast control, IGMP snooping, trunking, Port and Tagging VLANs, Port and IEEE 802.1x security, SNMP V3 and Https security, SNTP, web customization, user accounts
Status and diagnostic indicators	LEDs: U _{S1} , U _{S2} (redundant voltage supply), link and activity per port

Network expansion parameters

Cascading depth	Network, linear, and star structure: any
Maximum conductor length (twisted pair)	100 m

Supply voltage

Current consumption	359 mA (115 V AC from FL SWITCH 4800E-P5)
Inrush surge current	18.8 A (48 V DC from FL SWITCH 4800E-P1)

General

Mounting type	Rack mount, includes brackets
Type AX	Block design
Net weight	4470 g

Standards and Regulations

Type of test	Shock in acc. with EN 60068-2-27/IEC 60068-2-27
Test result	30g, 11 ms half-sine shock pulse
Type of test	Vibration resistance in acc. with EN 60068-2-6/IEC 60068-2-6
Test result	5g, 150 Hz, Criterion 3

Industrial Ethernet Switch - FL SWITCH 4824E-4GC - 2891072

Technical data

Standards and Regulations

Noise emission	EN 61000-6-4
Noise immunity	IEC 61850-3, IEEE 1613, EN 61000-6-2: 2005

Classifications

eCl@ss

eCl@ss 4.0	27250501
eCl@ss 4.1	27250501
eCl@ss 5.0	19030117
eCl@ss 5.1	19030117
eCl@ss 6.0	19170106
eCl@ss 7.0	19170106
eCl@ss 8.0	19170106
eCl@ss 9.0	19170106

ETIM

ETIM 3.0	EC000734
ETIM 4.0	EC000734
ETIM 5.0	EC000734
ETIM 6.0	EC000734

UNSPSC

UNSPSC 6.01	43172901
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	43222612

Approvals

Approvals

Approvals


UL Listed / cUL Listed / EAC / KC / cULus Listed

Ex Approvals

Industrial Ethernet Switch - FL SWITCH 4824E-4GC - 2891072

Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140403
cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 140403
EAC			RU *- DE.A*30.B.01735
KC		http://eng.kcc.go.kr/user/ehpMain.do	MSIP-REI- PCK-2891072
cULus Listed	