

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



PLC-INTERFACE for output functions, consisting of PLC-BSC.../ACT basic terminal block with screw connection and plug-in miniature solid-state relay, for mounting on DIN rail NS 35/7,5, 1 N/O contact, input: 24 V DC, output: 24 - 253 V DC/0.75 A

Product Features

- Actuator connected directly to relay module
- ▼ Time savings of up to 60 %
- ✓ No need for additional modular terminal blocks
- Efficient connection to system cabling using V8 adapter
- Relay modules with safe isolation according to DIN EN 50178 between coil and contact
- Space savings of up to 80 %





Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	38.0 g
Custom tariff number	85364190
Country of origin	Germany

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	6.2 mm
Height	80 mm
Depth	94 mm



Technical data

Ambient conditions

Ambient temperature (operation)	-25 °C 60 °C
Ambient temperature (storage/transport)	-25 °C 70 °C

Input data

Nominal input voltage U _N	24 V DC
Input voltage range in reference to U _N	0.8 1.2
Switching threshold "0" signal in reference to U _N	≤ 0.25
Switching threshold "1" signal in reference to U _N	≥ 0.8
Typical input current at U _N	9 mA
Typical response time	3 ms (at U _N)
Typical turn-off time	9 ms (at U _N)
Operating voltage display	Yellow LED
Type of protection	Protection against polarity reversal
	Free-wheeling diode
Protective circuit/component	Polarity protection diode
	Damping diode
Transmission frequency	10 Hz

Output data

Designation	Output data
Output voltage range	24 V AC 253 V AC
Limiting continuous current	0.75 A (see derating curve)
Maximum inrush current	30 A (10 ms)
Min. load current	10 mA
Leakage current	< 1 mA (in off state)
Max. load value	$4.5 A^2s$
Voltage drop at max. limiting continuous current	<1V
Output circuit	2-wire, floating
Type of protection	RCV circuit

Connection data, input side

Connection name	Input side
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross section solid	0.14 mm² 2.5 mm²
Conductor cross section flexible	0.14 mm² 2.5 mm²
AWG conductor cross section	26 14



Technical data

Connection data, output side

Connection name	Output side
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross section solid	0.14 mm² 2.5 mm²
Conductor cross section flexible	0.14 mm² 2.5 mm²
AWG conductor cross section	26 14

General

Test voltage input/output	2.5 kV (50 Hz, 1 min.)
Mounting position	any
Assembly instructions	In rows with zero spacing
Operating mode	100% operating factor
Flammability rating according to UL 94	V0
Designation	Standards/regulations
Standards/regulations	IEC 60664
	EN 50178
	IEC 62103
Rated surge voltage/insulation	Basic insulation
Pollution degree	2
Overvoltage category	III

Classifications

eCl@ss

eCl@ss 4.0	27371102
eCl@ss 4.1	27371102
eCl@ss 5.0	27371001
eCl@ss 5.1	27371001
eCl@ss 6.0	27371001
eCl@ss 7.0	27371001
eCl@ss 8.0	27371604

ETIM

ETIM 2.0	EC001504
ETIM 3.0	EC001504
ETIM 4.0	EC001504
ETIM 5.0	EC001504



Classifications

UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121542
UNSPSC 11	39121542
UNSPSC 12.01	39121542
UNSPSC 13.2	39121542


39121542
39121542
/ cULus Recognized / cULus Listed




Approvals

^
cUL Listed • • • • • • • • • • • • • • • • • • •
EAC
EAC
cULus Recognized C S Us
00Ed0 11C00g1112Cd # #
cULus Listed ***
COLUS LISTER TO THE COLUMN TO

Drawings





Circuit diagram

Phoenix Contact 2015 © - all rights reserved http://www.phoenixcontact.com