

## Router - TC MGUARD RS4000 3G VPN - 2903440

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Security device, WAN, and mobile phone interface. SD card slot. 10 VPN tunnels, intelligent firewall with full scope of functions, router with NAT/1:1 NAT, optional CIFS integrity monitoring. 4-port managed switch. 2 SIM card slots. GPS receiver.

### Your advantages

- ✓ High-speed mobile network interface with provider redundancy
- ✓ Integrated 4-port switch
- ✓ Maximum security with IPsec protocol on Layer 3
- ✓ Web-based management, SNMP
- ✓ Replaceable configuration memory
- ✓ RS-232 interface with COM server function for integrating serial devices
- ✓ Flexible routing
- ✓ Up to 10 parallel VPN tunnels (up to 250 possible with additional license as an option)
- ✓ Supports current certificates such as x509.v3
- ✓ Stateful inspection firewall for dynamic filtering
- ✓ Extended temperature range



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 752985
GTIN	4046356752985
Weight per Piece (excluding packing)	660.000 g
Custom tariff number	85176200
Country of origin	Germany

# Router - TC MGUARD RS4000 3G VPN - 2903440

## Technical data

### Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

### Dimensions

Width	45 mm
Height	130 mm
Depth	114 mm

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Altitude	≤ 5000 m (For restrictions, see the manufacturer's declaration for altitude operation)
Degree of protection	IP20

### General

Electrical isolation	VCC // PE
Test voltage data interface/data interface	1 kV (50 Hz, 1 min.)
Test voltage data interface/power supply	1 kV (50 Hz, 1 min.)
Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Net weight	600 g
Housing material	Metal
Color	silver
MTTF	567 Years (Telcordia standard, 25°C temperature, 21% operating cycle (5 days a week, 8 hours a day))
	269 Years (Telcordia standard, 40°C temperature, 34.25% operating cycle (5 days a week, 12 hours a day))
	114 Years (Telcordia standard, temperature 40 °C, operating cycle 100 % (7 days a week, 24 hours a day))
Degree of pollution	2

### Power supply

Supply voltage range	11 V DC ... 36 V DC (via pluggable COMBICON screw terminal block)
Max. current consumption	< 1.8 A (at 11 V DC (incl. 3 x 125 mA for the outputs))
Typical current consumption	< 320 mA (24 V DC)
Conductor cross section solid max.	2.50 mm <sup>2</sup>
Conductor cross section solid min.	0.20 mm <sup>2</sup>
Max. AWG conductor cross section, flexible	14
Min. AWG conductor cross section, flexible	24

## Router - TC MGUARD RS4000 3G VPN - 2903440

### Technical data

#### Serial interface

Interface 1	Ethernet interface, 10/100Base-T(X) in acc. with IEEE 802.3u
Interface	Ethernet
No. of ports	6
Connection method	RJ45
Transmission length	100 m (shielded twisted pair)
Protocols supported	TCP/IP, UDP/IP, FTP, HTTP
Auxiliary protocols	ARP, DHCP, PING (ICMP), SNMP V1, SMTP
Basic functions	Router with intelligent firewall and VPN for 10 tunnels (up to 250 supported with optional additional license), CIFS Integrity Monitoring (as an option), metal housing, slot for SD memory card
Interface 2	V.24 (RS-232) interface in acc. with ITU-T V.28, EIA/TIA-232, DIN 66259-1
Interface	RS-232
Connection method	D-SUB 9 plug
File format/coding	UART/NRZ: 8 Data, 1/2 Stop, None/Even/Odd Parity
Transmission length	15 m
Data flow control/protocols	Software handshake, Xon/Xoff or hardware handshake RTS/CTS
Serial transmission speed	9.6; 19.2; 38.4; 57.6; 115.2 kbps

#### Wireless interface

Interface description	GSM / GPRS / EDGE / UMTS / CDMA2000
Frequency	850 MHz (2 W (EGSM))
	900 MHz (2 W (EGSM))
	1800 MHz (1 W (EGSM))
	1900 MHz (1 W (EGSM))
	800 MHz (UMTS/HSPA B6)
	850 MHz (UMTS/HSPA B5)
	900 MHz (UMTS/HSPA B8)
	1900 MHz (UMTS/HSPA B2)
	2100 MHz (UMTS/HSPA B1)
	800 MHz (CDMA2000 EV-DO)
	1900 MHz (CDMA2000 EV-DO)
Data rate	≤ 14.4 Mbps (HSDPA)
	≤ 5.7 Mbps (HSUPA)
	≤ 3.1 Mbps (DL CDMA2000)
	≤ 1.8 Mbps (UL CDMA2000)
Antenna	50 Ω impedance SMA antenna socket
SIM interface 1	1.8 volt, 3 volt
SIM interface 2	1.8 volt, 3 volt

# Router - TC MGUARD RS4000 3G VPN - 2903440

## Technical data

### Wireless interface

GPRS	Class 12, Class B
	CS1 ... CS4
EDGE	Multislot Class 12
UMTS	HSPA 3GPP R6
Network function	4 time slots for receiving data, 4 time slots for transmitting data. The PIN is saved in the modem. After a voltage interruption, there is automatic redialing into the network. Integrated TCP/IP stack, firewall and VPN support, independent connection establishment.
Network check	LED bar graph to display receive quality
Protocols supported	GPS (Global Positioning System), GLONASS

### Function

Web-based management	yes
Management	Web-based management, SNMP

### Digital outputs

Output name	Digital output
Number of outputs	3
Voltage output signal	10 V DC ... 30 V DC (depending on the operating voltage)
Current output signal	≤ 125 mA (Short-circuit-proof)

### Digital inputs

Description of the input	Digital input
Number of inputs	3
Voltage input signal	10 V DC ... 30 V DC
Current input signal	5 mA

### Conformance/approvals

Designation	CE
Identification	CE-compliant
Designation	UL, USA/Canada
Identification	Class I, Div. 2, Groups A, B, C, D
Certificate	E357918
Designation	UL, USA
Identification	Class I, Zone 2, AEx nA IIC T4
Designation	UL, Canada
Identification	Class I, Zone 2, Ex nA IIC T4 Gc X
Designation	Corrosive gas test
Identification	ISA-S71.04-1985 G3 Harsh Group A

### Standards and Regulations

## Router - TC MGUARD RS4000 3G VPN - 2903440

### Technical data

#### Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Type of test	Free fall in acc. with IEC 60068-2-32
Test result	1 m
Type of test	Vibration resistance in acc. with EN 60068-2-6/IEC 60068-2-6
Test result	5g, 10...150 Hz, 2.5 h, in XYZ direction
Type of test	Shock in acc. with EN 60068-2-27/IEC 60068-2-27
Test result	Operation: 15g, 11 ms period, half-sine shock pulse
Type of test	Shock in acc. with EN 60068-2-27/IEC 60068-2-27
Test result	Storage: 30g, 11 ms period, half-sine shock pulse
Free from substances that could impair the application of coating	according to P-VW 3.10.7 57 65 0 VW-AUDI-Seat central standard
Standards/regulations	EN 61000-4-2
Contact discharge	± 6 kV (Test Level 3)
Standards/regulations	EN 61000-4-3
Frequency range	80 MHz ... 3 GHz (Test Level 3)
Standards/regulations	EN 61000-4-4
Comments	Criterion B
Standards/regulations	EN 61000-4-5
Signal	± 1 kV (Data line, asymmetrical)
Standards/regulations	EN 61000-6-4
	EN 61000-4-6
Frequency range	0.15 MHz ... 80 MHz


#### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

### Drawings

# Router - TC MGUARD RS4000 3G VPN - 2903440


Schematic diagram



Mounting

# Router - TC MGUARD RS4000 3G VPN - 2903440


Schematic diagram



Connecting the supply voltage

# Router - TC MGUARD RS4000 3G VPN - 2903440

Schematic diagram




Connection of the cables



# Router - TC MGUARD RS4000 3G VPN - 2903440


Schematic diagram



Remove SIM card holder

# Router - TC MGUARD RS4000 3G VPN - 2903440


Schematic diagram



Insert the SIM card

# Router - TC MGUARD RS4000 3G VPN - 2903440


Schematic diagram



Diagnostic and status indicators

## Router - TC MGUARD RS4000 3G VPN - 2903440

Application drawing



Redundant Internet connection via ADSL and the mobile network

### Classifications

eCl@ss

eCl@ss 4.0	27230200
eCl@ss 4.1	27230200
eCl@ss 5.0	19030100
eCl@ss 5.1	19030100
eCl@ss 6.0	19170100
eCl@ss 7.0	19170103
eCl@ss 8.0	19170103
eCl@ss 9.0	19170103

ETIM

ETIM 3.0	EC000310
ETIM 4.0	EC000740
ETIM 5.0	EC001478

# Router - TC MGUARD RS4000 3G VPN - 2903440

## Classifications

### ETIM

ETIM 6.0	EC001478
ETIM 7.0	EC001478

### UNSPSC

UNSPSC 6.01	30211506
UNSPSC 7.0901	39121008
UNSPSC 11	39121008
UNSPSC 12.01	39121008
UNSPSC 13.2	43222609

## Approvals

### Approvals

#### Approvals

UL Listed / cUL Listed / cULus Listed

#### Ex Approvals

UL Listed / cUL Listed / cULus Listed

### Approval details

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 238705
-----------	--	---	---------------

cUL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 238705
------------	--	---	---------------

cULus Listed			
--------------	--	--	--

## Accessories

### Accessories

Antenna

## Router - TC MGuard RS4000 3G VPN - 2903440

### Accessories

#### Antenna - TC ANT MOBILE/GPS - 2903590



Combined mobile phone GPS antenna with omnidirectional characteristic, 2 m antenna cable with SMA round plug (GSM/UMTS) and R-SMA round plug (GPS)

---

#### Antenna - PSI-GSM/UMTS-QB-ANT - 2313371



GSM UMTS antenna, with omnidirectional characteristic, 2 m antenna cable with SMA round connector

---

#### Antenna - TC ANT MOBILE WALL 5M - 2702273



Multiband mobile communication antenna with mounting bracket for outdoor installation, 5 m antenna cable with SMA circular connector, suitable for LTE/4G

---

### Coaxial cable

#### Antenna cable - PSI-CAB-GSM/UMTS- 5M - 2900980



Mobile network antenna cable, 5 m in length, SMA (male) -> SMA (female), 50 ohm impedance

---

#### Antenna cable - PSI-CAB-GSM/UMTS-10M - 2900981



Mobile network antenna cable, 10 m in length, SMA (male) -> SMA (female), 50 ohm impedance

---

## Router - TC MGUARD RS4000 3G VPN - 2903440

### Accessories

#### License

License - FL MGUARD LIC VPN-250 - 2700193



License for up to 250 additional VPN online connections

---

License - FL MGUARD LIC VPN-10 - 2700194



License for up to 10 additional VPN online connections

---

#### Media converter

FO converters - FL MC EF 1300 MM SC - 2902853



FO converter with SC duplex fiber optic connection (1300 nm), for converting 10/100Base-T(X) to multi-mode fiberglass (50/125 µm). Auto negotiation and auto MDI(X) function. Comprehensive link diagnostics. DIN-rail mountable, 18 ... 30 V DC supply.

---

#### Parameterization memory

Memory - SD FLASH 512MB - 2988146



Program and configuration memory, plug-in, 512 Mbyte.

---

#### Patch cable

## Router - TC MGuard RS4000 3G VPN - 2903440

### Accessories

Patch cable - FL CAT5 PATCH 0,5 - 2832263



Patch cable, CAT5, assembled, 0.5 m

---

Patch cable - FL CAT5 PATCH 2,0 - 2832289



Patch cable, CAT5, assembled, 2 m

---

Patch cable - FL CAT5 PATCH 10,0 - 2832629



Patch cable, CAT5, assembled, 10 m

---

### Plug

RJ45 connector - FL PLUG RJ45 GR/2 - 2744856



RJ45 connector, shielded, with bend protection sleeve, 2 pieces, gray for straight cables, for assembly on site. For connections that are not crossed, it is recommended that you use the connector set with gray bend protection sleeve.

---

RJ45 connector - FL PLUG RJ45 GN/2 - 2744571



RJ45 connector, shielded, with bend protection sleeve, 2 pieces, green for crossed cables, for assembly on site. For connections that are crossed, it is recommended that the connector set with green bend protection sleeves is used.

---



## Router - TC MGuard RS4000 3G VPN - 2903440

### Accessories

#### Protective cap

Dust protection - FL RJ45 PROTECT CAP - 2832991



Dust protection caps for RJ45 socket

---

#### Remote control software

License - MGuard SECURE VPN CLIENT LIC - 2702579



License for mGuard Secure VPN Client v11.x

---

#### Surge protection for transceiver systems

Surge protection device - CSMA-LAMBDA/4-2.0-BS-SET - 2800491



Attachment plug with Lambda/4 technology as surge protection for coaxial signal interfaces. Connection: Male/female SMA connectors.

---

Assembly tool - FL CRIMPTOOL - 2744869



Crimping pliers, for assembling the RJ45 plugs FL PLUG RJ45..., for assembly on site

---