

Interface module - VIP-3/PT/HD26SUB/M - 2904269


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOFACE module, with push-in connection and high density D-SUB miniature pin strip, for mounting on NS 35 rails, no. of pos.: 26



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 814782
GTIN	4046356814782
Weight per Piece (excluding packing)	152.000 g
Custom tariff number	85366990
Country of origin	United States

Technical data

Dimensions

Width	52 mm
Height	75.8 mm
Depth	63 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Nominal voltage U_N	25 V AC
	60 V DC
Max. perm. current (per branch)	1 A

Interface module - VIP-3/PT/HD26SUB/M - 2904269

Technical data

General

Number of positions	26
Status display	No
Mounting position	any

Connection data

Connection name	Field level
Connection in acc. with standard	IEC / EN
Connection method	Push-in connection
Stripping length	8 mm
Screw thread	M3
Number of positions	26
Conductor cross section solid	0.14 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.14 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 12

Connection data 2

Connection name	Controller level
Connection method	High density D-SUB pin strip
Number of connections	1
Number of positions	26

Standards and Regulations

Connection in acc. with standard	CSA
Standards/regulations	EN 50178
Rated surge voltage	1.2 kV
Pollution degree	2
Overvoltage category	II
Flammability rating according to UL 94	V0


Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"


Drawings

Interface module - VIP-3/PT/HD26SUB/M - 2904269

Dimensional drawing



Circuit diagram



Universal circuit diagram

Interface module - VIP-3/PT/HD26SUB/M - 2904269

Classifications

eCl@ss

eCl@ss 4.0	27250300
eCl@ss 4.1	27250300
eCl@ss 5.0	27250300
eCl@ss 5.1	27250300
eCl@ss 6.0	27242600
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152
eCl@ss 9.0	27141152

ETIM

ETIM 4.0	EC002780
ETIM 5.0	EC002780
ETIM 6.0	EC002780
ETIM 7.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121432

Approvals

Approvals

Approvals


CSA / UL Recognized / cUL Recognized / CSAus / EAC / cULus Recognized / cCSAus


Ex Approvals


Approval details


Interface module - VIP-3/PT/HD26SUB/M - 2904269

Approvals

CSA		http://www.csagroup.org/services-industries/product-listing/	2122203
Nominal voltage UN		105 V	
Nominal current IN		1 A	
mm ² /AWG/kcmil		26-14	

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
Nominal voltage UN		125 V	
Nominal current IN		1 A	
mm ² /AWG/kcmil		26-14	

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
Nominal voltage UN		125 V	
Nominal current IN		1 A	
mm ² /AWG/kcmil		26-14	

CSAus		http://www.csagroup.org/services-industries/product-listing/	2122203
Nominal voltage UN		105 V	
Nominal current IN		1 A	
mm ² /AWG/kcmil		28-14	

EAC		RU C- DE.A*30.B.01742
-----	---	--------------------------

Interface module - VIP-3/PT/HD26SUB/M - 2904269

Approvals

cULus Recognized



cCSAus

