

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Fuse modular terminal block, Number of positions: 1, Connection method: Screw connection, Cross section: 0.2 mm²- 6 mm², AWG: 24 - 10, Nominal current: 6.3 A, Nominal voltage: 500 V, Width: 8.2 mm, Fuse type: G / 5 x 20, Fuse type: Glass / ceramics / ..., Mounting type: NS 35/7,5, NS 35/15, NS 32, Color: black



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
Weight per Piece (excluding packing)	13.6 g
Custom tariff number	85369085
Country of origin	China

Technical data

General

Number of levels	1	
Number of connections	2	
Nominal cross section	4 mm²	
Color	black	
Insulating material	PA	
Flammability rating according to UL 94	V0	
Fuse	G / 5 x 20	
Fuse type	Glass / ceramics /	
Rated surge voltage	6 kV	
Degree of pollution	3	
Overvoltage category	III	
Insulating material group	I	
Maximum power dissipation	max. 1.6 W (With single arrangement of the fuse terminal block in the event of overload)	
Connection in acc. with standard	IEC 60947-7-3	



Technical data

General

Maximum load current	6.3 A (the current is determined by the fuse used)	
Nominal current I _N	6.3 A	
Nominal voltage U _N	500 V (As a fuse terminal block)	
Open side panel	Yes	
Number of positions	1	
Shock protection test specification	DIN EN 50274 (VDE 0660-514):2002-11	
Back of the hand protection	guaranteed	
Finger protection	guaranteed	
Oscillation, broadband noise test result	Test passed	
Test specification, oscillation, broadband noise	DIN EN 50155 (VDE 0115-200):2008-03	
Test spectrum	Service life test category 1, class B, body mounted	
Test frequency	$f_1 = 5 \text{ Hz to } f_2 = 150 \text{ Hz}$	
ASD level	1.857 (m/s²)²/Hz	
Acceleration	0.8g	
Test duration per axis	5 h	
Test directions	X-, Y- and Z-axis	
Shock test result	Test passed	
Test specification, shock test	DIN EN 50155 (VDE 0115-200):2008-03	
Shock form	Half-sine	
Acceleration	5 g	
Shock duration	30 ms	
Number of shocks per direction	3	
Test directions	X-, Y- and Z-axis (pos. and neg.)	
Relative insulation material temperature index (Elec., UL 746 B)	130 °C	
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C	
Static insulating material application in cold	-60 °C	

Dimensions

Width	8.2 mm
Length	58 mm
Height NS 35/7,5	50 mm
Height NS 35/15	57.6 mm
Height NS 32	55 mm

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	6 mm²
Conductor cross section flexible min.	0.2 mm ²



Technical data

Connection data

Conductor cross section flexible max.	4 mm²
Conductor cross section AWG min.	24
Conductor cross section AWG max.	10
Conductor cross section flexible, with ferrule without plastic sleeve min.	0.25 mm²
Conductor cross section flexible, with ferrule without plastic sleeve max.	4 mm²
Conductor cross section flexible, with ferrule with plastic sleeve min.	0.25 mm²
Conductor cross section flexible, with ferrule with plastic sleeve max.	2.5 mm²
Cross section with insertion bridge, solid max.	4 mm²
Cross section with insertion bridge, stranded max.	4 mm ²
2 conductors with same cross section, solid min.	0.2 mm²
2 conductors with same cross section, solid max.	1.5 mm²
2 conductors with same cross section, stranded min.	0.2 mm²
2 conductors with same cross section, stranded max.	1.5 mm²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	2.5 mm²
Cross section with insertion bridge, solid max.	4 mm²
Cross section with insertion bridge, stranded max.	4 mm²
Connection method	Screw connection
Stripping length	8 mm
Internal cylindrical gage	A4
Screw thread	M3
Tightening torque, min	0.6 Nm
Tightening torque max	0.8 Nm

Standards and Regulations

Connection in acc. with standard	IEC 60947-7-3
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	27141116
eCl@ss 4.1	27141116



Classifications

eCl@ss

eCl@ss 5.0	27141116
eCl@ss 5.1	27141116
eCl@ss 6.0	27141116
eCl@ss 7.0	27141116
eCl@ss 8.0	27141116

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000899
ETIM 4.0	EC000899
ETIM 5.0	EC000899

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / EAC / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details



Approvals

UL Recognized \$1			
	В	С	
mm²/AWG/kcmil	26-10	26-10	
Nominal current IN	16 A	16 A	
Nominal voltage UN	600 V	600 V	


cUL Recognized • • • • • • • • • • • • • • • • • • •			
	В	С	
mm²/AWG/kcmil	26-10	26-10	
Nominal current IN	16 A	16 A	
Nominal voltage UN	600 V	600 V	

EAC	
EAC	

cULus Recognized CSUs		

Drawings






Fuse terminal blocks in interconnected arrangement, block consisting of 5 fuse terminal blocks



Application drawing



Fuse terminal block in single arrangement, block consisting of one fuse terminal block and 4 feed-through terminal blocks

Phoenix Contact 2016 © - all rights reserved http://www.phoenixcontact.com