

Test adapter - PAIS-4-P/P GY - 3032794

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Test adapter, For 4 mm test plugs, color: gray

Your advantages

- ✓ Reliable contacting of test plugs with a 4 mm diameter in the function shaft
- ✓ Test adapter for accommodating safety test plugs with a 4 mm diameter

RoHS

COMPLETE RoHS

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 055626 011134
GTIN	4055626011134
Weight per Piece (excluding packing)	2.000 g
Custom tariff number	85366990
Country of origin	Poland

Technical data

Dimensions

Height	53.3 mm
Length	6.5 mm
Width	6 mm

General

Note	Only use in UDK 4 MTK-P/P and UK 5-MTK-P/P
	Do not plug in while the power is connected

Test adapter - PAIS-4-P/P GY - 3032794

Technical data

General

Color	gray
Material	Copper alloy
Ambient temperature (operation)	-40 °C ... 125 °C
Max. voltage	250 V
Maximum load current	10 A

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 10.0.1	27141148
eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141148
eCl@ss 8.0	27141148
eCl@ss 9.0	27141148

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC002255
ETIM 5.0	EC002555
ETIM 6.0	EC002555
ETIM 7.0	EC002555

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411

Test adapter - PAIS-4-P/P GY - 3032794

Classifications

UNSPSC

UNSPSC 13.2	20122006
UNSPSC 18.0	20122006
UNSPSC 19.0	20122006
UNSPSC 20.0	20122006
UNSPSC 21.0	20122006

Approvals


Approvals


Approvals

EAC / EAC

Ex Approvals

Approval details

EAC		RU C- DE.A*30.B.01742
-----	---	--------------------------

EAC		RU C- DE.BL08.B.00511
-----	---	--------------------------
