

Semi-conductor relay - OV-24DC/ 60DC/4 - 2982647

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Solid-state relay, for signal amplification and isolation of the control and load circuits, can be plugged in the solderable plug-in bases SIM-AMS or with PCB connection for mounting directly onto the PCB, input: 4.25-32 V DC, output: 1-60 V DC/4 A

Your advantages

- ✓ Compact dimensions
- ✓ No electromagnetic interference
- ✓ No wear, even at high switching frequencies
- ✓ High test voltage of up to 4 kV between control and load circuits
- ✓ Electrically insulated housing
- ✓ No contact bounce – no movable parts
- ✓ Switching power of up to 350 V DC/1 A, 60 V DC/4 A or 480 V AC/5 A

Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4046356131971
Weight per Piece (excluding packing)	24.700 g
Custom tariff number	85362010
Country of origin	China

Technical data

Dimensions

Width	10.5 mm
Height	43 mm
Depth	25.4 mm

Semi-conductor relay - OV-24DC/ 60DC/4 - 2982647

Technical data

Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
Ambient temperature (storage/transport)	-20 °C ... 80 °C

Input data

Nominal input voltage U_N	24 V DC
Input voltage range	4.25 V DC ... 32 V DC
Switching threshold "0" signal, voltage	< 1 V DC
Switching threshold "1" signal voltage	> 3.3 V DC
Typical input current at U_N	15 mA
Typical response time	< 100 μ s
Typical turn-off time	< 250 μ s
Transmission frequency	100 Hz

Output data

Output voltage range	1 V DC ... 60 V DC
Limiting continuous current	4 A (see derating curve)
Min. load current	1 mA
Leakage current	100 μ A
Surge current	25 A ($t_p = 1$ s)
Voltage drop at max. limiting continuous current	0.5 V
Output circuit	2-conductor
Type of protection	Reverse polarity protection
Protective circuit/component	Polarity protection diode

General

Test voltage input/output	4 kV (50 Hz, 1 min.)
Mounting position	any
Assembly instructions	Can be aligned with > 20 mm spacing
Operating mode	100% operating factor

Standards and Regulations

Connection in acc. with standard	CUL
Standards/regulations	EN 61000-4-2
	EN 61000-4-3
	EN 61000-4-4
	EN 55011
Insulation	Basic insulation

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
------------	--

Semi-conductor relay - OV-24DC/ 60DC/4 - 2982647

Technical data

Environmental Product Compliance

	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
--	---

Classifications

eCl@ss

eCl@ss 5.0	27371001
eCl@ss 5.1	27371000
eCl@ss 6.0	27371600
eCl@ss 7.0	27371604
eCl@ss 8.0	27371604
eCl@ss 9.0	27371604

ETIM

ETIM 2.0	EC001504
ETIM 3.0	EC001504
ETIM 4.0	EC001504
ETIM 5.0	EC001504
ETIM 6.0	EC001504
ETIM 7.0	EC001504

UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121542
UNSPSC 11	39121542
UNSPSC 12.01	39121542
UNSPSC 13.2	39122326

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / EAC / EAC / cULus Recognized

Ex Approvals

Semi-conductor relay - OV-24DC/ 60DC/4 - 2982647

Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 195083
cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 195083
EAC			TR_TS_D_00573_c
EAC			TR_TS_S_00010_c
cULus Recognized			