

## Electronic device circuit breaker - EC 1 12DC/3A S-R - 3000762


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Electronic circuit breaker, reset input and status output, nominal current: 3 A



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 708579
GTIN	4046356708579
Weight per Piece (excluding packing)	125.000 g
Custom tariff number	85362010
Country of origin	Germany

### Technical data

#### General

Mounting type	DIN rail: 35 mm
Color	black
Number of positions	1

#### Dimensions

Height	80 mm
Width	12.5 mm

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C (ordinary locations)
---------------------------------	---------------------------------------

#### Connection data

Conductor cross section solid min.	0.5 mm <sup>2</sup>
------------------------------------	---------------------

## Electronic device circuit breaker - EC 1 12DC/3A S-R - 3000762

### Technical data

#### Connection data

Conductor cross section solid max.	10 mm <sup>2</sup>
Conductor cross section flexible min.	0.5 mm <sup>2</sup>
Conductor cross section flexible max.	10 mm <sup>2</sup>
2 conductors with same cross section, solid min.	0.5 mm <sup>2</sup>
2 conductors with same cross section, solid max.	4 mm <sup>2</sup>
2 conductors with same cross section, stranded min.	0.5 mm <sup>2</sup>
2 conductors with same cross section, stranded max.	4 mm <sup>2</sup>
Connection method	Screw connection
Stripping length	10 mm
Screw thread	M4
Tightening torque, min	1.5 Nm
Tightening torque max	1.8 Nm

#### Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

### Classifications

#### eCl@ss

eCl@ss 4.0	27141100
eCl@ss 4.1	27141100
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141116
eCl@ss 8.0	27141116
eCl@ss 9.0	27141116

#### ETIM

ETIM 3.0	EC000899
ETIM 4.0	EC000943
ETIM 5.0	EC000899
ETIM 6.0	EC000899
ETIM 7.0	EC000899

# Electronic device circuit breaker - EC 1 12DC/3A S-R - 3000762

## Classifications

### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121411
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121410

## Approvals

### Approvals

#### Approvals

DNV GL / UL Recognized / UL Listed / UL Recognized / cUL Recognized / cUL Listed / EAC / cULus Listed

#### Ex Approvals


UL Recognized

### Approval details


DNV GL		<a href="https://approvalfinder.dnvgl.com/">https://approvalfinder.dnvgl.com/</a>	TAE00002HC
UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 140324
UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 140324
UL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 317172
cUL Recognized		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 140324

## Electronic device circuit breaker - EC 1 12DC/3A S-R - 3000762

### Approvals

cUL Listed		<a href="http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm</a>	FILE E 140324
------------	---	---	---------------

EAC			RU C- DE.A*30.B01546
-----	---	--	-------------------------

cULus Listed			
--------------	---	--	--

### Accessories

#### Accessories

#### Bridge

Continuous plug-in bridge - FBST 500 TMC-N GY - 0901028



Continuous plug-in bridge, number of positions: 1, mounting type: Plug-in mounting, Color: gray