

Cable duct - CD-HF 120X80 - 3240366

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable duct, light gray, halogen-free, consisting of upper part and mounting base, width: 120 mm, height: 80 mm, length: 2000 mm

The illustration shows the version in gray

Product Features

- Predetermined breaking point enables tool-free, burr-free removal of bars
- The wide, diagonal heads of the cable duct bars make it easy to fit the cover and hold it securely in place
- Fast and seamless creation of T and cross connections by means of an additional predetermined breaking point in the cable duct base
- Installed conductors are securely held in place by means of wire retaining clips that can be snapped onto bars on the side
- Cover is securely held in place for both horizontal and vertical mounting



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	8 pc
Custom tariff number	39259020
Country of origin	Germany

Technical data

Dimensions

Length (b)	2000 mm
Width (a)	120 mm
Height	80 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C
---------------------------------	------------------

General

Color	light gray
-------	------------

Cable duct - CD-HF 120X80 - 3240366

Technical data

General

Components	Halogen-free
Flammability rating according to UL 94	V0
Material	PC/ABS

Standards and Regulations

Halogen-free	yes
Connection in acc. with standard	CSA
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	27140602
eCl@ss 4.1	27140602
eCl@ss 5.0	27140602
eCl@ss 5.1	27140602
eCl@ss 6.0	27400703
eCl@ss 7.0	27400703
eCl@ss 8.0	27400703

ETIM

ETIM 2.0	EC000012
ETIM 3.0	EC000012
ETIM 4.0	EC000012
ETIM 5.0	EC000012

UNSPSC

UNSPSC 6.01	30101815
UNSPSC 7.0901	30101815
UNSPSC 11	30101815
UNSPSC 12.01	30101815
UNSPSC 13.2	30101815

Approvals

Approvals

Cable duct - CD-HF 120X80 - 3240366

Approvals



Approvals

CSA / UL Recognized / VDE Zeichengenehmigung

Ex Approvals


Approvals submitted

Approval details



Drawings

Dimensional drawing



Base perforation according to DIN EN 50085
