

Active module - UMK 22-REL 120/21-ST-TR - 5524235

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




VARIOFACE base module for G2R relay, 1PDT

UMK 22 REL 24 VAC/21-21 shown

Why buy this product

- Safe isolation between coil and contact side

Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 684545
GTIN	4046356684545
Weight per Piece (excluding packing)	59.600 g
Custom tariff number	85364190
Country of origin	United States

Technical data

Dimensions

Width	22.5 mm
Height	77 mm
Depth	50 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 65 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Coil side

Nominal input voltage U_N	120 V AC
Typical input current at U_N	31 mA
Typical response time	15 ms
Typical release time	5 ms

Active module - UMK 22-REL 120/21-ST-TR - 5524235

Technical data

Coil side

Operating voltage display	LED
---------------------------	-----

Contact side

Contact type	1 PDT
Contact material	AgCdO
Maximum switching voltage	250 V AC (30 V DC)
Limiting continuous current	10 A

General

Test voltage relay winding/relay contact	5 kV (50/60 Hz, 1 min.)
Operating mode	100% operating factor
Mechanical service life	1 x 10 ⁷ cycles
Mounting position	any
Assembly instructions	In rows with zero spacing

Connection data input side

Connection name	Coil side
Connection method	Screw connection
Stripping length	7 mm
Conductor cross section solid	0.14 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross section AWG	30 ... 14

Connection data output side

Connection name	Contact side
Connection method	Screw connection
Stripping length	7 mm
Conductor cross section solid	0.14 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross section AWG	30 ... 14