

## Box mounting base - TMCP SOCKET M - 0916589

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Modular socket element, 2-position, for holding two circuit breakers, each with a single position

### Why buy this product

- The TMCP SOCKET M base element is used to mount TMCP ... and ECP ... plug-in circuit breakers on DIN rails
- Using connections 13 and 14 in the termination elements, a signal loop can be created via all circuit breakers quickly and without the need for additional wiring
- User-friendly spring-cage connection
- Large-surface labeling options make it easier to assign the circuit breakers to the modules
- Flexible structure with any number of positions
- Individual protection thanks to free combination of both circuit breaker types on a single module
- Separate signal request for each circuit breaker
- Potential distribution by means of bridges
- All electrical connections of the main and signal contacts are located in the base

### Key Commercial Data

Packing unit	10 STK
GTIN	 4 017918 600921
Sales Key	04

### Technical data

#### General

Number of levels	1
Number of connections	2
Mounting type	DIN rail: 35 mm
Color	black
Insulating material	PA-F
Flammability rating according to UL 94	V0

#### Electrical data

Fuse type	Automatic device
Rated surge voltage	2.5 kV
Rated voltage	433 V (AC)

## Box mounting base - TMCP SOCKET M - 0916589

### Technical data

#### Electrical data

	65 V (DC)
Operating voltage	433 V (AC)
Nominal current $I_N$	50 A (LINE input)
	25 A (LOAD output)
Rated current $I_N$	50 A
Rated insulation voltage $U_i$	1500 V
Degree of pollution	2

#### Dimensions

Height	115 mm
Width	25 mm
Depth	110.5 mm
Height NS 35/7,5	110.5 mm
Height NS 35/15	118 mm

#### Connection data

Connection method	Spring-cage connection
-------------------	------------------------

### Classifications

#### eCl@ss

eCl@ss 4.0	27141116
eCl@ss 4.1	27141116
eCl@ss 5.0	27141116
eCl@ss 5.1	27141116
eCl@ss 6.0	27141116
eCl@ss 7.0	27141116
eCl@ss 8.0	27141116

#### ETIM

ETIM 2.0	EC000899
ETIM 3.0	EC000899
ETIM 4.0	EC000472
ETIM 5.0	EC000899

#### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121411
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

## Box mounting base - TMCP SOCKET M - 0916589

### Approvals

#### Approvals

---

#### Approvals

UL Recognized / cUL Recognized / EAC / EAC / cULus Recognized

---


#### Ex Approvals


---

#### Approvals submitted

---

#### Approval details

UL Recognized 

cUL Recognized 

EAC

EAC

cULus Recognized 

Phoenix Contact 2016 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>