

Cable tie - WT-E HF 4,8X200 - 3240720

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable binders ideal for permanent fastening to virtually any surface, with fastening lug for screwing or fixing with rivets

Key Commercial Data

| | |
|--------------------------------------|----------|
| Packing unit | 1 pc |
| Minimum order quantity | 100 pc |
| Weight per Piece (excluding packing) | 1.8 g |
| Custom tariff number | 39269097 |
| Country of origin | Taiwan |

Technical data

Dimensions

| | |
|----------------|------------------|
| Length (b) | 200 mm |
| Width (a) | 4.8 mm |
| Hole diameter | 5.20 mm |
| Cable diameter | 3.5 mm ... 44 mm |

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 85 °C |
| Ambient temperature (assembly) | -10 °C ... 60 °C |
| Optimum ambient temperature (storage/transport) | 23 °C 50 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat. |
| Short-term temperature | 110 °C |

General

| | |
|-------|-------------|
| Color | transparent |
|-------|-------------|

Cable tie - WT-E HF 4,8X200 - 3240720

Technical data

General

| | |
|--|--------------------------------|
| Type | Internal teeth |
| Components | free from silicone and halogen |
| Flammability rating according to UL 94 | V2 |
| Material | PA 6.6 |

Standards and Regulations

| | |
|--|----|
| Resistance to UV radiation | no |
| Flammability rating according to UL 94 | V2 |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27140702 |
| eCl@ss 4.1 | 27140702 |
| eCl@ss 5.0 | 27140702 |
| eCl@ss 5.1 | 27140702 |
| eCl@ss 6.0 | 27140702 |
| eCl@ss 7.0 | 27140702 |
| eCl@ss 8.0 | 27140702 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC000046 |
| ETIM 4.0 | EC000046 |
| ETIM 5.0 | EC000046 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30212109 |
| UNSPSC 7.0901 | 27121703 |
| UNSPSC 11 | 27121703 |
| UNSPSC 12.01 | 27121703 |
| UNSPSC 13.2 | 27121703 |