

Antenna cable - RAD-PIG-RSMA/N-5 - 2702140

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Antenna cable, 5 m in length; N (male) -> RSMA (male), impedance 50 ohms



The illustration shows a version of the product

Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 988407

Technical data

Dimensions

Fixed cable length	5 m
External diameter	4.95 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

General

Connection method	RSMA (male)
	N (male)
Cable type	195
Minimum bending radius	12.70 mm
Frequency range	900 MHz
	2.4 GHz
	5 GHz
Impedance	50 Ω

Attenuation

868 / 900 MHz	2.02 dB
2.4 GHz	3.32 dB
5 GHz	4.83 dB

Antenna cable - RAD-PIG-RSMA/N-5 - 2702140

Classifications

eCl@ss

eCl@ss 4.0	27230207
eCl@ss 4.1	27250312
eCl@ss 5.0	27242208
eCl@ss 5.1	27061802
eCl@ss 6.0	27242208
eCl@ss 7.0	27242208
eCl@ss 8.0	27060310

ETIM

ETIM 2.0	EC000019
ETIM 3.0	EC000019
ETIM 4.0	EC000019
ETIM 5.0	EC001682

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>