

# Marker for terminal blocks - UCT-TM 6 - 0828736

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)


Marker for terminal blocks, Sheet, white, Unlabeled, Can be labeled with: Thermomark C, Bluemark, Mounting type: Snap into tall marker groove, For terminal block width: 6.2 mm, Lettering field: 5.6 x 10.5 mm



## Why buy this product

- The multi-section marking strips are easy to fit and can be easily separated if required
- Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and precisely using the THERMOMARK CARD and the BLUEMARK LED
- The sheets provide space for including function texts
- The UCT-TM... UniCard labeling range includes markers for products with tall marker grooves

## Key commercial data

Packing unit	0
Minimum order quantity	10
Catalog page	Page 73 (CL2-2011)
GTIN	 4 046356 522465
Custom tariff number	39269097
Country of origin	GERMANY

## Technical data

### General

Note	Can be labeled via thermal transfer
Length (b)	10.5 mm
Height	4.76 mm
Width (a)	5.6 mm
Color	white
Inflammability class according to UL 94	V0
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Components	free from silicone and halogen
Material	PC
Number of individual labels	60
Number of individual labels per row	10
RoHS compliant	Yes
Halogen-free	Yes

# Marker for terminal blocks - UCT-TM 6 - 0828736

## Technical data

### General

Silicone-free	Yes
Cadmium-free	Yes
Printability	Thermal transfer
Device	5146464 THERMOMARK CARD
Device	5146451 THERMOMARK CARD-US-MAG1
Ink ribbon	0801371 THERMOMARK-RIBBON 110-TC
Test specification weathering-resistance	Following ISO 4892-2:2006-02 + A1:2009-07
Duration of test	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2006-10
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:1997-06
Climate level	KFW 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	IEC 61010-1:2010-06
Result	Test passed

## Classifications

### eclass

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27149103
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137

### etim

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761

### unspsc

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

## Accessories

### Accessories

## Marker for terminal blocks - UCT-TM 6 - 0828736

### Accessories

Magazine - THERMOMARK CARD-UCT-MAG1 - 5146480



Magazine for the THERMOMARK CARD printer, for accommodating UCT sheets (UCT-TM..., UCT1-TM..., UCT5-TM...)

---

© Phoenix Contact 2012 - all rights reserved  
<http://www.phoenixcontact.com>