

## Industrial Ethernet Switch - FL SWITCH SFN 5TX - 2891152

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Ethernet switch, 5 TP RJ45 ports, automatic detection of data transmission speed of 10 or 100 Mbps (RJ45), autocrossing function

One port is located on the bottom

### Why buy this product

- M
- Local diagnostic indicators with LEDs
- The switch also offers cable locking and port blocking
- RJ45 ports support a transmission speed of 10/100 Mbps; fiber optic ports support 100 Mbps
- QoS-prioritized (Quality of Service) messages

### Ethernet

#### Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 100793

#### Technical data

##### Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

##### Dimensions

Width	30 mm
Height	120 mm
Depth	70 mm

##### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Air pressure (operation)	86 kPa ... 5 kPa (up to 1500 m above mean sea level)

# Industrial Ethernet Switch - FL SWITCH SFN 5TX - 2891152

## Technical data

### Ambient conditions

Air pressure (storage/transport)	66 kPa ... 108 kPa (up to 3500 m above mean sea level)
----------------------------------	--

### Interfaces

Interface 1	Ethernet (RJ45)
No. of ports	5 (RJ45 ports)
Connection method	RJ45
Note on connection method	Auto negotiation and autocrossing
Transmission physics	Ethernet in RJ45 twisted pair
Transmission speed	10/100 MBit/s

### Function

Basic functions	Unmanaged switch / auto negotiation, complies with IEEE 802.3, store and forward switching mode
Status and diagnostic indicators	LEDs: U <sub>S</sub> , link and activity per port

### Network expansion parameters

Cascading depth	Network, linear, and star structure: any
Maximum conductor length (twisted pair)	100 m

### Supply voltage

Supply voltage	24 V DC
Residual ripple	3.6 V <sub>PP</sub> (within the permitted voltage range)
Supply voltage range	9 V DC ... 32 V DC
Typical current consumption	90 mA (at U <sub>S</sub> = 24 V DC)
Max. current consumption	205 mA (at 9 V DC)

### General

Mounting type	DIN rail
Type AX	Block design
Net weight	416.1 g
Housing material	Aluminum

### Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2004/108/EC
Developed in acc. with standard	IEC 61000-6.2
Test standard	IEC 61000-4-2 (ESD)
Test result	Criterion B
Test standard	IEC 61000-4-3 (immunity to radiated interference)
Test result	Criterion A
Test standard	IEC 61000-4-4 (burst)
Test result	Criterion B
Test standard	IEC 61000-4-5 (surge)
Test result	Criterion B
Test standard	IEC 61000-4-6 (immunity to conducted interference)

# Industrial Ethernet Switch - FL SWITCH SFN 5TX - 2891152

## Technical data

### Standards and Regulations

Test result	Criterion A
Test standard	IEC 61000-4-8 (immunity to magnetic fields)
Test result	Criterion A
Test standard	EN 55022 (emitted interference)
Test result	Criterion A
Test section	500 V DC 1 min.
Noise emission	EN 61000-6-4
Noise immunity	EN 61000-6-2:2005
Vibration (storage/transport)	5g, 150 Hz, in acc. with IEC 60068-2-6
Free from substances that could impair the application of coating	In acc. with VW specification
Vibration (operation)	In acc. with IEC 60068-2-6: 5g, 150 Hz

## Classifications

### eCl@ss

eCl@ss 4.0	27250501
eCl@ss 4.1	27250501
eCl@ss 5.0	27250501
eCl@ss 5.1	27250501
eCl@ss 6.0	19170106
eCl@ss 7.0	19170106
eCl@ss 8.0	19170106

### ETIM

ETIM 2.0	EC000734
ETIM 3.0	EC000734
ETIM 4.0	EC000734
ETIM 5.0	EC000734

### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	43201410

## Approvals

### Approvals

# Industrial Ethernet Switch - FL SWITCH SFN 5TX - 2891152

## Approvals

### Approvals

UL Listed / cUL Listed / EAC / EAC / KC / cULus Listed

---

### Ex Approvals


UL Listed / cUL Listed / cULus Listed

---

### Approvals submitted

---

## Approval details

UL Listed 

cUL Listed 

EAC

EAC

KC

cULus Listed 

---

Phoenix Contact 2016 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>