



Extract from the online catalog

CABLE-FLK20/OE/0,14/ 100

Order No.: 2305305

The illustration shows a 50-pos. version



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2305305>

Round cable assembled with a 20-pos. socket strip and an open end. On the open end, the wires are labeled with 1 to 20 and have ferrules, cable length: 1 m

Commercial data	
EAN	4046356038980
Pack	1 pcs.
Customs tariff	85444290
Weight/Piece	0.0983 KG
Catalog page information	Page 261 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
06/08/2006

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data	
General	
Nominal voltage U_N	< 50 V AC
	60 V DC
Max. current carrying capacity per path	1 A
Max. conductor resistance	0.16 Ω /m

CABLE-FLK20/OE/0,14/ 100 Order No.: 2305305
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2305305>

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Number of positions	20
Number of positions, control side	20
Number of connectors, control side	0
Number of positions, module side	20
Number of connectors, modul side	1
Fixed cable length	1 m
Single wire, cross section	0.14 mm ²
AWG	26
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
Test voltage	0.8 kV
External diameter	7.6 mm
Cable, preassembly	Insulation displacement, IEC 60352-4/DIN EN 60352-4
Shielding	no

Certificates / Approvals

Certifications applied for: UL / CUL

CABLE-FLK20/OE/0,14/ 100 Order No.: 2305305
<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2305305>

Address

PHOENIX CONTACT Deutschland GmbH
Flachmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;

onlinecomponents.com