

Antenna - ANT-OMNI-2459-02 - 2701408

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Omnidirectional antenna, 2.4 GHz/5 GHz, 2.5/5 dBi gain, linear vertical polarization, opening angle 2.4 GHz h/v 360°/30°, 5 GHz h/v 360°/16°, N (male), IP68; matching cable with panel feed-through Order No. 2701402

Why buy this product

- For mobile or point-to-multipoint applications with a small range

Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 746731

Technical data

Dimensions

Length	180 mm
Diameter	23 mm

Ambient conditions

Degree of protection	IP68
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

General

With connecting cable	No
Frequency range	2.4 GHz
	5 GHz
	2.4 GHz ... 2.5 GHz
	5.15 GHz ... 5.83 GHz
Horizontal beamwidth	360 ° (At 2.4 GHz)
Vertical beamwidth	30 ° (At 2.4 GHz)
Polarization	Linear vertical
Impedance	50 Ω
Gain	2.5 dBi (2.4 GHz)
	5 dBi (5 GHz)

Antenna - ANT-OMNI-2459-02 - 2701408

Technical data

General

Connection method	N (male)
-------------------	----------

Classifications

eCl@ss

eCl@ss 4.0	27240409
eCl@ss 4.1	27240409
eCl@ss 5.0	27242215
eCl@ss 5.1	27242208
eCl@ss 6.0	27242208
eCl@ss 7.0	27242208
eCl@ss 8.0	19070105
eCl@ss 9.0	19070105

ETIM

ETIM 3.0	EC001423
ETIM 4.0	EC000416
ETIM 5.0	EC001698

UNSPSC

UNSPSC 6.01	20142601
UNSPSC 7.0901	20142601
UNSPSC 11	20142601
UNSPSC 12.01	20142601
UNSPSC 13.2	20142601

Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>