

Shrink sleeve - WMS 4,8 (30X9)R - 0800375

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Shrink sleeve, Roll, white, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL: without print, perforated, mounting type: slide-on, cable diameter range: 1.6 ... 4.8 mm, lettering field size: 30 x 9 mm, Number of individual labels: 500

Your advantages

- ✓ The sleeves are pre-assembled for optimum use of material
- ✓ WMS ... shrink sleeves provide permanent and captive conductor and cable marking
- ✓ The conductor to be marked is simply threaded through the sleeve and fixed by shrinking the sleeve
- ✓ The sleeves remain flexible after shrinking
- ✓ The shrink sleeves provide additional electrical insulation and mechanical protection for the conductors
- ✓ Up to four markers per sleeve are separated by perforations
- ✓ UL 224 (125°C, 600 V, all tubing)
- ✓ CSA.C22.2 No. 198.1 (125°C, 600 V, all tubing)



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 626446
GTIN	4046356626446
Weight per Piece (excluding packing)	300.000 g
Custom tariff number	39173200
Country of origin	China

Technical data

Dimensions

Length (b)	30 mm
Width (a)	9 mm

Shrink sleeve - WMS 4,8 (30X9)R - 0800375

Technical data

Dimensions

Cable diameter	1.6 mm ... 4.8 mm
----------------	-------------------

Ambient conditions

Ambient temperature (operation)	-55 °C ... 125 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.

General

Color	white
Base element material	polyolefine
Type	Shrink sleeve
Components	halogen-free
Material	Polyolefine
Shrink rate	3:1
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing	without print
Number of individual labels	500
Number of individual labels per row	2
Marking mounting type	slide-on

Classifications

eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 11.0	27281102
eCl@ss 4.0	24190200
eCl@ss 4.1	24190200
eCl@ss 5.0	27400100
eCl@ss 5.1	27400100
eCl@ss 6.0	27400100
eCl@ss 7.0	27400105
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC001530
ETIM 4.0	EC000217
ETIM 6.0	EC001530
ETIM 7.0	EC001530

Shrink sleeve - WMS 4,8 (30X9)R - 0800375

Classifications

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Approvals

Approvals


Approvals

CSA / UL Recognized

Ex Approvals

Approval details

CSA		http://www.csagroup.org/services-industries/product-listing/	252259
-----	---	---	--------

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 310982
---------------	---	---	---------------

Accessories

Accessories

Ink ribbon

Shrink sleeve - WMS 4,8 (30X9)R - 0800375

Accessories

Ink ribbon - THERMOMARK-RIBBON 64-WMSU - 0801360



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 64 mm, color: black

Ink ribbon - THERMOMARK-RIBBON 110-WMSU - 0801358



Ink ribbon, for roll printer for printing product groups WMS... and WMS-2 HF..., width: 110 mm, color: black

Printing system accessories

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm
