


CE Elastomeric Cable Ties



- Elastic material provides a flexible tie body that safely contours around cable bundle, preventing over-tensioning of data cables to maintain network integrity
- UL 94V-0 material provides greater flame resistance; meets stringent telecommunication flammability requirements (such as NEBS GR-63-CORE)
- Soft material has no sharp edges; protects the installer and the cable bundle
- High coefficient of friction grips and prevents lateral movement along cable bundle
- Releasable and re-usable to accommodate frequent moves, adds, and changes
- Halogen-free, non-toxic, and environmentally safe material will not release toxic or corrosive gases upon combustion
- Locking head design; the tapered tip threads into locking head to speed productivity; industry-accepted intuitive tie design

Part Number	Length		Width		Thickness		Max. Bundle Dia.		Min. Loop Tensile Str.		Recommended Installation Tool	Std. Pkg. Qty.	Std. Ctn. Qty.
	In.	mm	In.	mm	In.	mm	In.	mm	Lbs.	N			
ERT2M-C20	8.5	216	0.500	12.70	0.090	2.29	2.35	59.7	18	80	Hand install only	100	1000
ERT3M-C20	11.0	279	0.500	12.70	0.090	2.29	3.00	76.2	18	80	Hand install only	100	1000
ERT4.5M-C20	16.0	406	0.500	12.70	0.090	2.29	4.50	114	18	80	Hand install only	100	1000

UL US LISTED CE Contour-Ty® Cable Ties – Nylon 6.6



- Unique design prevents wire and cable damage
- Low profile head avoids snags and reduces overall bundle size
- Outside teeth and smooth round edges protect cable jacket – ideal for high vibration applications
- Parallel-entry limits exposure to sharp edges and protects workers' arms/hands
- Fully enclosed head for consistent strength
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation



Part Number	Length		Width		Thickness		Max. Bundle Dia.		Min. Loop Tensile Str.		Recommended Installation Tool	Bulk Pkg. Qty.	Bulk Ctn. Qty.
	In.	mm	In.	mm	In.	mm	In.	mm	Lbs.	N			
CBR1M-M	4.1	104	0.098	2.5	0.038	1.0	1.00	25	18	80	GTS, GTSL, GS2B, PTS, PPTS, STS2	1000	50000
CBR1.5M-M	5.6	142	0.098	2.5	0.042	1.1	1.50	38	18	80		1000	50000
CBR2M-M	7.2	183	0.098	2.5	0.042	1.1	2.00	51	18	80		1000	25000

Intermediate Cross Section – Plenum-Rated

CBR1.5I-M	5.9	150	0.140	3.6	0.040	1.0	1.50	38	40	178	GTS, GTSL, GS2B, PTS, PPTS, STS2	1000	25000
CBR3I-M	10.4	264	0.140	3.6	0.052	1.3	3.00	76	40	178		1000	10000
CBR4I-M	13.6	345	0.140	3.6	0.052	1.3	3.6	102	40	178		1000	10000

Standard Cross Section – Plenum-Rated

CBR2S-M	7.6	193	0.190	4.8	0.044	1.1	2.00	51	50	222	GTS, GTSL, GS2B, GTH, GS4H, PTS, PTH, PPTS, STS2, STH2	1000	10000
CBR3S-M	10.8	274	0.190	4.8	0.052	1.3	3.00	76	50	222		1000	5000
CBR4S-M	14.0	356	0.190	4.8	0.052	1.3	4.00	102	50	222		1000	5000

Heavy-Standard Cross Section – Plenum-Rated

CBR2HS-D	8.0	203	0.250	6.4	0.058	1.4	2.00	51	85	378	GTH, GS4H, GS4EH, PTH, STH2, ST3EH	500	5000
-----------------	-----	-----	-------	-----	-------	-----	------	----	----	-----	------------------------------------	-----	------

Light-Heavy Cross Section – Plenum-Rated

CBR4LH-TL	14.6	371	0.300	7.6	0.070	1.8	7.6	102	120	534	GTH, GS4H, GS4EH, PTH, STH2, ST3EH	250	2500
CBR6LH-C	20.9	531	0.300	7.6	0.070	1.8	6.00	152	120	534		100	2000