

**Search Results**

- Evaluate
  - FAQ's
- Design a Solution
  - Catalog Cut Sheet
  - PDFGJS660U Prod
  - Part Drawings
  - PDFV Block Jump..
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor
- Install & Maintain
  - Installation Instructions
  - PDFEquipment Gr..

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

Text Search: 'RGEJ660U'

Your search criteria matched only one product, shown below

**RGEJ660U**



- Bond network equipment to grounding strip or grounding busbar
- Jumper kit available with both ends factory terminated to provide a bolt -on solution
- Jumper kit available with one end factory terminated to attach to the grounding strip or grounding busbar; free end accommodates unique equipment terminations
- Use jumpers with 90° bent lug, on grounding strip side, for high density grounding requirements up to one ground point per RU
- Use jumpers with 45° bent lugs, on grounding strip side, for improved cable management
- Use 24" jumpers when network equipment ground point is located near the grounding strip side of the rack or cabinet
- Use 36" jumpers when network equipment ground point is located away from the grounding strip side of the rack
- Engineered to comply with US and International grounding requirements

Part Number	RGEJ660U
Part Description	#6 AWG (16mn <sup>2</sup> ) jumper, 60 in. (1524mm) L, preterminated with two straight slotted lugs to provide a bolt-on solution for grounding network equipment.
Length (In.)	60
Length (m)	1.52
Length (mm)	1524
Angle	Straight
CE Compliant	No
Pricing Description	Equipment Grounding Jumper
Min. Order UOM	KT
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	<input type="button" value="e"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.