

TS-ED Series 105°C, 3000 hours


- High ripple current capability for demanding inverter applications
- 2 and 3 pin versions available
- RoHS compliant PVC and RoHS compliant PET sleeve options




Rated Working Voltage:	200 ~ 250 VDC	400 ~ 450 VDC																																						
Operating Temperature:	-40 ~ +105°C	-25 ~ +105°C																																						
Nominal Capacitance:	220~2200 µF	56 ~ 560µF																																						
Capacitance Tolerance:	± 20%																																							
Dissipation Factor: (120 Hz, +20°C)	15% max.																																							
Leakage Current:	3√CV (µA) max. after 5 minutes; C = Capacitance in µF, V = WV																																							
Ripple Current Multipliers:	<table border="1"> <tr> <th>Frequency(Hz):</th> <th>50</th> <th>60</th> <th>100~120</th> <th>500</th> <th>1k</th> <th>10k</th> </tr> <tr> <td>16~100WV:</td> <td>0.93</td> <td>0.95</td> <td>1.0</td> <td>1.05</td> <td>1.08</td> <td>1.15</td> </tr> <tr> <td>160~450WV:</td> <td>0.75</td> <td>0.8</td> <td>1.0</td> <td>1.2</td> <td>1.25</td> <td>1.4</td> </tr> </table>	Frequency(Hz):	50	60	100~120	500	1k	10k	16~100WV:	0.93	0.95	1.0	1.05	1.08	1.15	160~450WV:	0.75	0.8	1.0	1.2	1.25	1.4	<table border="1"> <tr> <th colspan="5">Ripple Current Ambient Temperature Factors*</th> </tr> <tr> <td>Temperature (°C):</td> <td>105°C</td> <td>85°C</td> <td>70°C</td> <td>60°C</td> <td>≤45°C</td> </tr> <tr> <td>Multiplier:</td> <td>1.0</td> <td>1.7</td> <td>2.0</td> <td>2.2</td> <td>2.35</td> </tr> </table>	Ripple Current Ambient Temperature Factors*					Temperature (°C):	105°C	85°C	70°C	60°C	≤45°C	Multiplier:	1.0	1.7	2.0	2.2	2.35
Frequency(Hz):	50	60	100~120	500	1k	10k																																		
16~100WV:	0.93	0.95	1.0	1.05	1.08	1.15																																		
160~450WV:	0.75	0.8	1.0	1.2	1.25	1.4																																		
Ripple Current Ambient Temperature Factors*																																								
Temperature (°C):	105°C	85°C	70°C	60°C	≤45°C																																			
Multiplier:	1.0	1.7	2.0	2.2	2.35																																			
Endurance:	3000 hours at +105°C with maximum specified ripple current (see page4)																																							

*Use of temperature ripple current multipliers may limit life to the hours specified for the maximum operating temperature.

Part Number System



Dimensions in millimeters



Design and specifications are subject to change without notice.

Contact the factory or your sales representative for technical specifications before purchase and/or use. When safety concerns arise, please contact Panasonic immediately for technical consultation.

TS-ED Standard Ratings

Part numbers shown with 2 pins and 4.0mm length terminals

Cap. (μ F)	Size (mm) D x L	Max 105°C R.C. (A_{rms})		20°C ESR (Ω , max.)		Panasonic Part Number (By Sleeve Style)	
		120Hz	10kHz~	120Hz	20kHz	PVC with Top Plate	PET without Top Plate
200 VDC Working, 250 VDC Surge							
270	22 x 25	1.42	2.03	0.553	0.249	EETED2D271HA	EETED2D271HJ
330	22 x 30	1.56	2.23	0.452	0.203	EETED2D331HA	EETED2D331HJ
390	22 x 30	1.71	2.44	0.383	0.172	EETED2D391HA	EETED2D391HJ
	25 x 25	1.71	2.44	0.383	0.172	EETED2D391JA	EETED2D391JJ
470	22 x 35	1.85	2.64	0.317	0.143	EETED2D471HA	EETED2D471HJ
	25 x 30	1.85	2.64	0.317	0.143	EETED2D471JA	EETED2D471JJ
560	22 x 40	2.14	3.05	0.266	0.120	EETED2D561HA	EETED2D561HJ
	25 x 30	2.14	3.05	0.266	0.120	EETED2D561JA	EETED2D561JJ
	30 x 25	2.14	3.05	0.266	0.120	EETED2D561KA	EETED2D561KJ
680	22 x 45	2.42	3.45	0.219	0.099	EETED2D681HA	EETED2D681HJ
	25 x 35	2.42	3.45	0.219	0.099	EETED2D681JA	EETED2D681JJ
	30 x 30	2.42	3.45	0.219	0.099	EETED2D681KA	EETED2D681KJ
820	22 x 50	2.63	3.76	0.182	0.082	EETED2D821HA	EETED2D821HJ
	25 x 40	2.63	3.76	0.182	0.082	EETED2D821JA	EETED2D821JJ
	30 x 30	2.63	3.76	0.182	0.082	EETED2D821KA	EETED2D821KJ
	35 x 25	2.63	3.76	0.182	0.091	EETED2D821LA	EETED2D821LJ
1000	25 x 45	2.84	4.06	0.149	0.067	EETED2D102JA	EETED2D102JJ
	30 x 35	2.84	4.06	0.149	0.067	EETED2D102KA	EETED2D102KJ
	35 x 30	2.84	4.06	0.149	0.067	EETED2D102LA	EETED2D102LJ
1200	30 x 40	3.13	4.47	0.124	0.062	EETED2D122KA	EETED2D122KJ
	35 x 35	3.13	4.47	0.124	0.062	EETED2D122LA	EETED2D122LJ
1500	30 x 50	3.56	5.08	0.099	0.050	EETED2D152KA	EETED2D152KJ
	35 x 40	3.56	5.08	0.099	0.050	EETED2D152LA	EETED2D152LJ
1800	35 x 45	3.84	5.48	0.083	0.041	EETED2D182LA	EETED2D182LJ
2200	35 x 50	4.12	5.89	0.068	0.033	EETED2D222LA	EETED2D222LJ
250 VDC Working, 300 VDC Surge							
220	22 x 30	1.28	1.83	0.678	0.305	EETED2E221HA	EETED2E221HJ
270	22 x 30	1.42	2.03	0.553	0.249	EETED2E271HA	EETED2E271HJ
	25 x 25	1.42	2.03	0.553	0.249	EETED2E271JA	EETED2E271JJ
330	22 x 35	1.64	2.34	0.452	0.203	EETED2E331HA	EETED2E331HJ
	25 x 30	1.56	2.23	0.452	0.203	EETED2E331JA	EETED2E331JJ
390	22 x 40	1.72	2.45	0.383	0.172	EETED2E391HA	EETED2E391HJ
	25 x 30	1.71	2.44	0.383	0.172	EETED2E391JA	EETED2E391JJ
	30 x 25	1.71	2.44	0.383	0.172	EETED2E391KA	EETED2E391KJ
470	22 x 45	1.85	2.64	0.317	0.143	EETED2E471HA	EETED2E471HJ
	25 x 35	1.85	2.64	0.317	0.143	EETED2E471JA	EETED2E471JJ
	30 x 30	1.85	2.64	0.317	0.143	EETED2E471KA	EETED2E471KJ
560	25 x 40	2.14	3.05	0.266	0.120	EETED2E561JA	EETED2E561JJ
	30 x 30	2.14	3.05	0.266	0.120	EETED2E561KA	EETED2E561KJ
	35 x 25	2.14	3.05	0.266	0.133	EETED2E561LA	EETED2E561LJ
680	25 x 45	2.42	3.45	0.219	0.099	EETED2E681JA	EETED2E681JJ
	30 x 35	2.42	3.45	0.219	0.099	EETED2E681KA	EETED2E681KJ
	35 x 30	2.42	3.45	0.219	0.110	EETED2E681LA	EETED2E681LJ
820	30 x 40	2.63	3.76	0.182	0.082	EETED2E821KA	EETED2E821KJ
	35 x 35	2.63	3.76	0.182	0.091	EETED2E821LA	EETED2E821LJ
1000	30 x 50	2.84	4.06	0.149	0.067	EETED2E102KA	EETED2E102KJ
	35 x 40	2.84	4.06	0.149	0.067	EETED2E102LA	EETED2E102LJ
1200	35 x 45	3.13	4.47	0.124	0.062	EETED2E122LA	EETED2E122LJ
1500	35 x 50	3.56	5.08	0.099	0.050	EETED2E152LA	EETED2E152LJ
400 VDC Working, 450 VDC Surge							
82	22 x 25	0.80	1.14	1.617	0.728	EETED2G820HA	EETED2G820HJ
100	22 x 30	0.91	1.30	1.326	0.597	EETED2G101HA	EETED2G101HJ
	25 x 25	0.91	1.30	1.326	0.597	EETED2G101JA	EETED2G101JJ
120	22 x 35	1.02	1.46	1.105	0.497	EETED2G121HA	EETED2G121HJ
	25 x 30	1.02	1.46	1.105	0.497	EETED2G121JA	EETED2G121JJ
150	22 x 40	1.07	1.53	0.884	0.398	EETED2G151HA	EETED2G151HJ
	25 x 30	1.07	1.53	0.884	0.398	EETED2G151JA	EETED2G151JJ
	30 x 25	1.07	1.53	0.884	0.398	EETED2G151KA	EETED2G151KJ
180	22 x 45	1.12	1.60	0.737	0.332	EETED2G181HA	EETED2G181HJ
	25 x 35	1.12	1.60	0.737	0.332	EETED2G181JA	EETED2G181JJ
	30 x 30	1.12	1.60	0.737	0.332	EETED2G181KA	EETED2G181KJ
220	22 x 50	1.42	2.03	0.603	0.271	EETED2G221HA	EETED2G221HJ
	25 x 40	1.42	2.03	0.603	0.271	EETED2G221JA	EETED2G221JJ
	30 x 30	1.42	2.03	0.603	0.271	EETED2G221KA	EETED2G221KJ

Design and specifications are subject to change without notice.

Contact the factory or your sales representative for technical specifications before purchase and/or use.

When safety concerns arise, please contact Panasonic immediately for technical consultation.

TS-ED Standard Ratings (continued)

Part numbers shown with 2 pins and 4.0mm length terminals

Cap. (μ F)	Size (mm) D x L	Max 105°C R.C. (A_{rms})		20°C ESR (Ω , max.)		Panasonic Part Number (By Sleeveing Style)	
		120Hz	10kHz~	120Hz	20kHz	PVC with Top Plate	PET without Top Plate
400 VDC Working, 450 VDC Surge (continued)							
220	35 x 25	1.42	2.03	0.603	0.271	EETED2G221LA	EETED2G221LJ
270	25 x 45	1.56	2.23	0.491	0.221	EETED2G271JA	EETED2G271JJ
	30 x 35	1.56	2.23	0.491	0.221	EETED2G271KA	EETED2G271KJ
	35 x 30	1.56	2.23	0.491	0.221	EETED2G271LA	EETED2G271LJ
330	30 x 40	1.71	2.44	0.402	0.181	EETED2G331KA	EETED2G331KJ
	35 x 30	1.71	2.44	0.402	0.181	EETED2G331LA	EETED2G331LJ
390	30 x 45	1.85	2.64	0.340	0.153	EETED2G391KA	EETED2G391KJ
	35 x 35	1.85	2.64	0.340	0.153	EETED2G391LA	EETED2G391LJ
470	35 x 40	2.01	2.87	0.282	0.127	EETED2G471LA	EETED2G471LJ
560	35 x 45	2.35	3.36	0.237	0.107	EETED2G561LA	EETED2G561LJ
420 VDC Working, 470 VDC Surge							
68	22 x 25	0.67	0.95	1.950	0.878	EETED2S680HA	EETED2S680HJ
82	22 x 30	0.76	1.08	1.617	0.728	EETED2S820HA	EETED2S820HJ
	25 x 25	0.76	1.08	1.617	0.728	EETED2S820JA	EETED2S820JJ
100	22 x 30	0.80	1.14	1.326	0.597	EETED2S101HA	EETED2S101HJ
	25 x 25	0.80	1.14	1.326	0.597	EETED2S101JA	EETED2S101JJ
120	22 x 35	0.91	1.30	1.105	0.497	EETED2S121HA	EETED2S121HJ
	25 x 30	0.91	1.30	1.105	0.497	EETED2S121JA	EETED2S121JJ
150	22 x 40	1.02	1.46	0.884	0.398	EETED2S151HA	EETED2S151HJ
	25 x 35	1.02	1.46	0.884	0.398	EETED2S151JA	EETED2S151JJ
	30 x 25	1.02	1.46	0.884	0.398	EETED2S151KA	EETED2S151KJ
180	22 x 45	1.07	1.53	0.737	0.332	EETED2S181HA	EETED2S181HJ
	25 x 40	1.07	1.53	0.737	0.332	EETED2S181JA	EETED2S181JJ
	30 x 30	1.07	1.53	0.737	0.332	EETED2S181KA	EETED2S181KJ
	35 x 25	1.07	1.53	0.737	0.332	EETED2S181LA	EETED2S181LJ
220	25 x 45	1.12	1.60	0.603	0.271	EETED2S221JA	EETED2S221JJ
	30 x 35	1.12	1.60	0.603	0.271	EETED2S221KA	EETED2S221KJ
	35 x 30	1.12	1.60	0.603	0.271	EETED2S221LA	EETED2S221LJ
270	25 x 50	1.42	2.03	0.491	0.221	EETED2S271JA	EETED2S271JJ
	30 x 40	1.42	2.03	0.491	0.221	EETED2S271KA	EETED2S271KJ
	35 x 30	1.42	2.03	0.491	0.221	EETED2S271LA	EETED2S271LJ
330	30 x 45	1.72	2.45	0.402	0.181	EETED2S331KA	EETED2S331KJ
	35 x 35	1.72	2.45	0.402	0.181	EETED2S331LA	EETED2S331LJ
390	30 x 50	1.85	2.64	0.340	0.153	EETED2S391KA	EETED2S391KJ
	35 x 40	1.85	2.64	0.340	0.153	EETED2S391LA	EETED2S391LJ
470	35 x 45	1.97	2.82	0.282	0.127	EETED2S471LA	EETED2S471LJ
450 VDC Working, 500 VDC Surge							
56	22 x 25	0.67	0.95	2.368	1.066	EETED2W560HA	EETED2W560HJ
68	22 x 30	0.76	1.08	1.950	0.878	EETED2W680HA	EETED2W680HJ
	25 x 25	0.76	1.08	1.950	0.878	EETED2W680JA	EETED2W680JJ
82	22 x 30	0.80	1.14	1.617	0.728	EETED2W820HA	EETED2W820HJ
	25 x 25	0.80	1.14	1.617	0.728	EETED2W820JA	EETED2W820JJ
100	22 x 35	0.91	1.30	1.326	0.597	EETED2W101HA	EETED2W101HJ
	25 x 30	0.91	1.30	1.326	0.597	EETED2W101JA	EETED2W101JJ
120	22 x 40	1.02	1.46	1.105	0.497	EETED2W121HA	EETED2W121HJ
	25 x 35	1.02	1.46	1.105	0.497	EETED2W121JA	EETED2W121JJ
	30 x 25	1.02	1.46	1.105	0.497	EETED2W121KA	EETED2W121KJ
150	22 x 45	1.07	1.53	0.884	0.398	EETED2W151HA	EETED2W151HJ
	25 x 40	1.07	1.53	0.884	0.398	EETED2W151JA	EETED2W151JJ
	30 x 30	1.07	1.53	0.884	0.398	EETED2W151KA	EETED2W151KJ
	35 x 25	1.07	1.53	0.884	0.398	EETED2W151LA	EETED2W151LJ
180	22 x 50	1.12	1.60	0.737	0.332	EETED2W181HA	EETED2W181HJ
	25 x 40	1.12	1.60	0.737	0.332	EETED2W181JA	EETED2W181JJ
	30 x 30	1.12	1.60	0.737	0.332	EETED2W181KA	EETED2W181KJ
	35 x 25	1.12	1.60	0.737	0.332	EETED2W181LA	EETED2W181LJ
220	25 x 45	1.42	2.03	0.603	0.271	EETED2W221JA	EETED2W221JJ
	30 x 35	1.42	2.03	0.603	0.271	EETED2W221KA	EETED2W221KJ
	35 x 30	1.42	2.03	0.603	0.271	EETED2W221LA	EETED2W221LJ
270	30 x 40	1.72	2.45	0.491	0.221	EETED2W271KA	EETED2W271KJ
	35 x 35	1.72	2.45	0.491	0.221	EETED2W271LA	EETED2W271LJ
330	30 x 50	1.85	2.64	0.402	0.181	EETED2W331KA	EETED2W331KJ
	35 x 40	1.85	2.64	0.402	0.181	EETED2W331LA	EETED2W331LJ
390	35 x 40	1.97	2.82	0.340	0.153	EETED2W391LA	EETED2W391LJ
470	35 x 50	2.47	3.53	0.282	0.127	EETED2W471LA	EETED2W471LJ

Design and specifications are subject to change without notice.

Contact the factory or your sales representative for technical specifications before purchase and/or use.

When safety concerns arise, please contact Panasonic immediately for technical consultation.