


specifications

Modular furniture faceplates shall be multiple port densities that snap directly into TIA/EIA-569-B standard furniture communications openings of other popular modular furniture manufacturers. The faceplates accept individual modules which are secured from the rear and when seated, are flush with the faceplate.



MINI-COM® Modular Furniture Faceplates

technical information

| | | |
|--------------------|--------------|---|
| Dimensions: | CFFP4**: | HxWxD=1.70x2.90x.40in. (43.18x73.66x10.16mm) |
| | CFFPL4**: | HxWxD=1.70x2.90x.40in. (43.18x73.66x10.16mm) |
| | CFFPA2**: | HxWxD=1.70x2.90x.70in. (43.18x73.66x19.33mm) |
| | MFFPE**: | HxWxD=2.19x3.69x.50in. (55.62x93.73x12.7mm) |
| | CFFPHM4**: | HxWxD=2.08x3.64x.40in. (52.83x92.96x10.16mm) |
| | CFFPEBSL4**: | HxWxD=2.56x3.71x.92in. (67.3x94.23x23.37mm) |
| | CFFPKE3**: | HxWxD=1.95x3.65x1.25in. (49.53x92.71x31.75mm) |
| | CFFPE3**: | HxWxD=1.70x3.50x.90in. (43.18x88.9x22.86mm) |

Mounting options: Industry standard TIA/EIA opening 1.345" to 1.405" H x 2.670" W, maximum thickness .09"

Material: ABS plastic

key features and ...benefits

| | |
|--|---|
| Modularity | Accepts all <i>MINI-COM</i> Modules; individual modules snap in and out |
| Sloped solution | Protects bend radius of copper and fiber cables (CFFPA2** and CFFPEBSL4**) |
| Extender adapter | Increased bend radius of cables for protection and works with part numbers CFFP4, CFFPL4 and CFFPE3 |
| Works with computer printable labels | Complies with TIA/EIA 606-A specifications |
| Available with optional label/label cover | Some versions come with a built in label/label cover pocket for easy identification of ports |

applications

The 2 and 4 position furniture faceplates (CFFP4**, CFFPL4** and CFFPA2**) are used in work areas with modular furniture which have the TIA/EIA standard furniture outlet opening. The standard opening is often provided by the furniture manufacturer or can be punched in the field with a special punch tool.

Modular furniture manufacturers like Herman Miller™ and Knoll® have custom openings for various models of furniture. The CFFPHM4** can be used

with Herman Miller Action Office 2 & 3 and Baseline furniture series. The CFFPEBSL4** is designed to work with the Ethospace Beltline series, and is a 4 position sloped faceplate. Knoll Equity furniture can utilize CFFPKE3** which is a 3 position furniture faceplate that is extended off the face of the furniture. Also offered is a comparable 3 position faceplate (CFFPE3**) which adapts to the Knoll's Morrison Series, in addition to the TIA/EIA standard opening.

Knoll is a registered trademark of Knoll Inc., East Greenville, PA.
Herman Miller is a trademark of Herman Miller, Inc., Zeeland, MI.

Visit our website at: www.panduit.com/ncg

Modular Furniture Faceplates (for standard openings)

| | |
|---------------------------------------|----------|
| 4 module space: | CFFP4** |
| 4 module space with label: | CFFPL4** |
| 2 module space sloped: | CFFPA2** |
| 3 module space Knoll Morrison: | CFFPE3** |

Modular Furniture Faceplates (for custom openings)

| | |
|--|-------------|
| 4 module space Herman Miller: | CFFPHM4** |
| 4 module space sloped Herman Miller Ethospace Beltline with label & icon slots: | CFFPEBSL4** |
| 3 module space Knoll Equity: | CFFPKE3** |

Accessories

| | |
|---|---------|
| Modular furniture faceplate extender: | MFFPE** |
| <small>(For use with CFFP4, CFFPL4 and CFFPE3.)</small> | |
| Punch die: | MFFD |
| <small>(For use with plastic or metal furniture. Requires hydraulic driver such as a GreenLee #7804SB.)</small> | |


Adhesive dot-matrix/laser label: CPPLF-5

| | |
|--|----------|
| Non-adhesive laser label kit with adhesive carrier: | NWL4-KIT |
| LS3E adhesive label: | L3CPLFWH |


**Substitute: IW = Off White
IG = International Gray
BL = Black

MINI-COM® Modular Furniture Faceplates


2 Module Space Angled (CFFPA2)




4 Module Space (CFFP4 & CFFPL4)




Extender (MFFPE)




4 Module Space Herman Miller (CFFPHM4)




4 Module Space Herman Miller Ethospace Beltline (CFFPEBSL4)



3 Module Space Knoll Equity (CFFPKE3)



3 Module Space Knoll Morrison (CFFPE3)



Dimensions are in inches (Dimensions in parentheses are millimeters)

Our products are warranted to be free from defects in material and workmanship at the time of sale but our obligation under this warranty is limited to the replacement of any product proved to be defective within 6 months (for product) or 90 days (for tools) from the date of delivery. Tool warranty is void if Panduit tools are modified, altered or misused in any way. Use of Panduit tooling with any product other than the specified Panduit products for which the tool was designed, constitutes misuse. Before using, user shall determine the suitability of the product for his intended use and user assumes all risk and liability whatsoever in connection therewith.

This warranty is made in lieu of and excludes all other warranties, expressed or implied. THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR USE ARE SPECIFICALLY EXCLUDED. Neither seller nor manufacturer shall be liable for any other injury, loss or damage whether direct or consequential, arising out of the use of, or the inability to use, the product.

The information contained in this literature is based on our experience to date and is believed to be reliable. It is intended as a guide for use by persons having technical skill at their own discretion and risk. We do not guarantee favorable results or assume any liability in connection with its use. Dimensions contained herein are for reference purposes only. For specific dimensional requirements consult the factory. This publication is not to be taken as a license to operate under, or a recommendation to infringe any existing patents. This supersedes and voids all previous literature, etc.



WORLD HEADQUARTERS
PANDUIT CORP.
Tinley Park, Illinois, USA
Phone: 888-506-5400, ext. 6914
708-532-1800, ext. 6914
Fax: 708-460-2897
Email: ncginfo@panduit.com
Internet: www.panduit.com/ncg

**For Pricing and Further Information —
Contact your local authorized
PANDUIT PAN-NET™ Distributor or Sales Office**

PANDUIT CANADA
Div. of PANDUIT CORP.
Markham, Ontario
Phone: 905-475-6922

EUROPEAN HEADQUARTERS
PANDUIT EUROPE LTD.
London, UK
Phone: 44(0) 208-601-7200

ASIAN HEADQUARTERS
PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
Phone: (65) 379 6700

PANDUIT CORP.
Japan Branch
Phone (81) (3) 3767-7011

PANDUIT MEXICO/LATIN AMERICA
& CARIBBEAN
Phone: (52) 3 666-2501

PANDUIT (AUST.) PTY. LTD.
Phone: (61) 3-9794 9020