


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	\triangle_B "X" \triangle_E	\triangle_A "X" TOL.	\triangle_B "T" \triangle_E	\triangle_A "T" TOL.	\triangle_C "R" \triangle_E	\triangle_C "R" TOL.	LENGTH	WEIGHT
D2H6	1.79 (45.3)	$\pm .03 (.8)$.07 (1.7)	$\pm .012 (.3)$.24 (6.0)	$\pm .03 (.8)$	72.00 in	.096 LB/FT (.143 Kg/M)
D3H6	2.74 (69.7)	$\pm .05 (1.3)$.09 (2.2)	$\pm .016 (.4)$.26 (6.5)	$\pm .03 (.8)$	$\pm .13$ in	.165 LB/FT (.245 Kg/M)
D4H6	3.53 (89.8)	$\pm .06 (1.5)$.11 (2.8)	$\pm .020 (.5)$.26 (6.5)	$\pm .03 (.8)$	(1829mm ± 3.3 mm)	.285 LB/FT (.426 Kg/M)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. THIS PART IS INTENDED TO BE USED WITH MOUNTING BASE DB-C IN ORDER TO SUCCEED AS A DIVIDER WALL APPLICATION.
3. DIMENSIONS IN PARENTHESIS ARE IN METRIC.



CAD FILENAME/LAYERS D34301_DC_DH6_F_DIV_03A.prt

										PANDUIT CORP. TINLEY PARK, ILLINOIS	
										SOLID DIVIDER WALL FOR WIRING DUCT & FIBER DUCT (D2H6, D3H6, D4H6) CUSTOMER DRAWING	
4	5/24/10	LEF	MKBE	F. REMOVED PARTS D1H6 & D1.5H6	34301-05	MKBE	MKBE			UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) \pm (.XXX) \pm (.XX) $\pm .06 (1.5)$ ANGLES \pm	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
3	4/14/04	JCST	JKG	E. MODIFIED DIM. "X" & "R" IN VIEW AND CHART D. MODIFIED TITLE	34301-05	HIW	HIW				
2	3-11-94	DW	CEF	C. REV'D DIM "T" AND ADDED DIM "R".	34301-05	CEF	CEF				
1	1-28-94	DW	CEF	B. REVISED DIMENSIONS. A. ADDED TOLERANCES.	34301-05	CEF					
R	5-5-93	DW	KRKE	RELEASED TO PRODUCTION	34301-05	CEF				DRAWN BY DW DATE 5-5-93 CHK'D KRKE	SCALE NONE DRAWING NO. 34301-05 DWG SIZE A
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP			