


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	MAX. COMBINED BUNDLE DIA. D1 + D2 in (mm)	A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT lbs/100 pcs. (g)
PLB2S	1.8 (45.7)	.052 (1.3)	.190 (4.8)	.465 (11.8)	.220 (5.6)	.320 (8.1)	7.6 (193)	50 (222)	STANDARD	.34 (154)
PLB3S	3.0 (76.2)	.052 (1.3)	.190 (4.8)	.465 (11.8)	.220 (5.6)	.337 (8.6)	11.8 (300)	50 (222)	STANDARD	.47 (214)
PLB4S	4.1 (104.1)	.052 (1.3)	.190 (4.8)	.465 (11.8)	.220 (5.6)	.337 (8.6)	14.8 (376)	50 (222)	STANDARD	.58 (262)

NOTES:

\*1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

										DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS			
										SS-21645_05.PRT			
										PANDUIT CORP. TINLEY PARK, ILLINOIS			
										BOW-TY CABLE TIES PLB SERIES			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .0005 (.XXX) ± .020 (.51) (.XX) ± .02 (.5) ANGLES ± .0005			
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.			
---	-----	---	ⓑ ADDED REF. TO D1 & D2 DIM.			-----	---			DRAWN BY KEM	MAT'L: NYLON 6/6	SCALE NONE	
5	2/18/99	KET	Ⓐ ADDED REF. TO C DIM.			21645	5			DATE 4/6/87	NYLON 6/6	DRAWING NO. SS-21645	DWG A
4	12/18/95	DKN	JCC	"C" DIM. .465 (11.8) WAS .438 (11.1)			21645	4				CHK'D HVP	SIZE A
REV	DATE	BY	CHK	DESCRIPTION			ECN	R	CUST	SUP			