



Quam

VANDAL RESISTANT

CIS8/8

INTERCOM ASSEMBLY

**2-Gang Hands-Free Station, 8 Ohm Speaker,
Vandal Resistant, Stainless Steel, NO Button**

GENERAL DESCRIPTION

The **CIS8/8** is a 2-gang, vandal resistant "hands free - no call button" station with a 2.5" square frame loudspeaker, 2.35-oz. ceramic magnet, 8 Ohm impedance, and a moisture-resistant cone. Three (3) interwoven, steel security screens are mounted between the faceplate and loudspeaker. Tamper-resistant, 6-32 x 1" Pin In Torx® hardware included.

INTENDED USE - Indoor or Protected Outdoor Environment



Program Material | Signal Tones and Voice

AUDIO SPECIFICATIONS

Average Sensitivity	87 dB SPL, 1W/ 1M
Magnet Type & Weight	BeFe Ceramic, 2.35 oz. Nominal
Frequency Response	200 Hz - 8 kHz EIA 426A Standard
Nominal Coverage Angle	90° Included Angle, -6 dB / 2 kHz, Half space
Audio Connection	9" Stripped and Tinned Leads

RECOMMENDED QUAM COMPONENTS

Enclosures | *Surface Mount* : SE6GVP, SE7GVP



WIRE LENGTH NOT TO SCALE

Recommended construction sequences, installation instructions, and A&E Specifications are available in various formats in the Specs and Diagrams section at: www.QuamSpeakers.com



QUAM-NICHOLS COMPANY, INC.
234 East Marquette Road. Chicago, IL. 60637
t: 1-800-NEED-NOW (800-633-3669)
f: 1-888-NEED-NOW (888-633-3669)
e: NeedNow@QNC.com
www.QuamSpeakers.com

©2017 Quam-Nichols Company reserves the right to make changes and/or improvements to its products at any time and without notice.