


## 650038-000 Product Details



650038-000

TE Internal Number: 650038-000

[Active](#)

### MiniSeal Splices

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Splice Type = Butt [in-line]
- Silver Wire Material, Tin Wire Material
- Crimp Barrel Size = 304 - 1510 CMA
- Side 1 Max. # of Wires = 6 [2 per hole]
- Side 2 Max. # of Wires = 2

[View all Features](#)

#### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [In-line Splice Sealing System, 2 or 3 to 1 Splice: T...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Splice Type](#) = Butt [in-line]
- [Wire Material](#) = Silver, Tin
- Connection Type = Crimp
- Color Code = Red

#### Body Related Features:

- [Crimp Barrel Size \(CMA \[mm<sup>2</sup>\]\)](#) = 304 - 1510 [0.15 - 0.75]
- Crimp Barrel Plating = Tin

#### Housing Related Features:

- [MIL Specification \[MIL-S-81824\]](#) = No
- Side 1 Max. # of Wires = 6 [2 per hole]
- Side 2 Max. # of Wires = 2
- Side 1 Sealing Insert I.D. (mm [in]) = 2.36 [0.093]
- Side 2 Sealing Insert I.D. (mm [in]) = 4.06 [0.160]

#### Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- Operating Temperature (Max.) (°C) = 150

#### Operation/Application:

- Application Type = Wire to wire splicing

#### Other:

- Brand = Raychem

[BOOKMARK](#)

#### Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

#### Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

#### Customer Support

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)