

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Catalog Cut Sheet
 - PDFDMV1-63P-LY
 - Part Drawings
 - PDFMetric Male..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'DMNF163FIM-L'

Your search criteria matched only one product, shown below

DMNF1-63FIM-L



- Male tab couples with (all 6.3mm x 0.8mm) female disconnects
- Fully insulated design provides protection from electrical shorts
- Male tab can be inserted and removed from the female disconnect without the use of tools for lower installed cost
- Internal barrel serrations assure good wire contact and maximum tensile strength
- Maximum insulation temperature 221°F (105°C)
- Rated up to 600 V

Part Number	DMNF163FIML
RoHS Compliancy Status	Compliant
Note	DMNF163FIML replaces DMNF163FIMC
Part Description	Metric Male Disconnect, 0.5– 1.0mm ² wire range, 6.3mm x .8mm tab size, nylon fully insulated, funnel entry.
Product Type	Disconnects - Metric
Color	Red
Height (mm)	7.03
Length (mm)	22.9
Width (mm)	10.3
CE Compliant	No
Insulation	Nylon
Max. Ins. (mm)	3.38
Panduit Color Code	Red
Plating Type	Nickel
Pricing Description	Metric Male Disconnect, nylon fully insulated, 0.5– 1.0mm ² wire range, 6.3 x .8mm tab size, funnel entry
Tab Size (mm)	6.3 x 0.8
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)
Tool	CT-1525, CT-2500
Wire Range (mm ²)	0.5 – 1.0
Min. Order UOM	PC
Min. Order Qty.	50
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.