





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORPORATION.

PANDUIT PART NO.	DIMENSIONS					USE WITH THESE TIES	APPLICATION INFORMATION		WEIGHT lbs/100pcs (g)/100pcs
	A	B (REF)	C	D	E (REF)		HOLE DIAMETER	PANEL THICKNESS	
ATM-W187	0.350 (8.9)	.80 (20.5)	.576 (14.6)	.270 (7.0)	.22 (5.7)	MINIATURE INTERMEDIATE	.170-.197 (4.3)-(4.9)	.120 (3.0) MAX	.112 (51)
ATM-W250			.655 (16.6)		.30 (7.6)				.225-.260 (5.7)-(6.6)



NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- FOR USE WITH AUTOMATIC CABLE TIE TOOL HEAD AND ACCESSORIES



SCALE 1:1

DIMENSIONS IN PARENTHESSES ARE METRIC (mm)	
CAD FILENAME/LAYERS G03473BA_DC_GB3473BA/07A	
<b>PANDUIT</b> CORP.	TINLEY PARK, ILLINOIS
AUTO TIE MOUNT ATM-W_	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25) (.XX) ±0.02 (.5) ANGLES ±5°	
UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
DRAWN BY DJSM	MAT'L: HEAT STABILIZED NYLON 6/6
DATE 07/03/08	SCALE 2:1 UNLESS NOTED
CHK'D	DRAWING NO. GB3473BA
	DWG A SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
07A	08-06-09	GDH		CONTROL DRAWING UPDATE - NO DIMENSIONAL CHANGE	GB3473BA	07A		
06A	08/11/08	DJSM		WIDENED WINDOW TO ACCOMMODATE INTERMEDIATE TIE	GB3473BA	06A		
05A	08/08/08	DJSM		INITIAL RELEASE	GB3473BA	05A		