



Network and Electrical Solutions

UNIFIED PHYSICAL INFRASTRUCTURESM

Worldwide |



Home

Industries

Solutions

Products

Partners

Support

About Us

Careers

-Search-

Entire Site



Search Results

Evaluate

- Brochures
- PDF-Enhanced Sta ..
- FAQ's

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips Within Results

Text Search: 'MLT2S-L'

Your search criteria matched only one product, shown below

MLT2S-L



The *Pan-Steel*[®] system provides a strong durable method of bundling and fastening. Stainless steel cable ties can be used in virtually all indoor, outdoor and underground (including direct burial) applications. They are especially well suited for network bundling of data and power cables. High strength, non-flammability, fully rounded edges and exclusive easy thread lead-in design provide the ultimate support for network cables.

- Self-locking head design speeds installation and locks into place at any length along the tie
- Provides a strong, durable method of cable bundling
- Can be used in a wide range of indoor, outdoor, and underground (including direct burial) applications
- Smooth surfaces and rounded edges assures cable protection and worker safety
- Available in AISI 304 stainless steel for general-purpose applications
- Available in AISI 316 stainless steel for the most corrosive environments

Product Specifications

- Material: Type 304 or 316 stainless steel
- Temperature range: -112°F (-80°C) to 1000°F (538°C)
- Water absorption: none
- Flammability: non-flammable
- Ultraviolet resistance: excellent
- Chemical resistance: excellent
- Radiation resistance: 2×10^8 rads
- Loop tensile strength range: 200-900 lbs. (890-4005N) (see chart for sizes)
- Fully rounded edges and smooth surfaces

• Estimated outdoor service life of 40 years	
▪ Part Number	MLT2S-L
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Stainless steel cable tie, standard, 2" (50mm) max bundle diameter.
▪ Material	Stainless Steel Type 304
▪ Color	natural
▪ UL Listed	Yes
▪ Length (In.)	7.9
▪ Length (mm)	201
▪ Width (In.)	.18
▪ Width (mm)	4.6
▪ Cross Section	Standard
▪ Max. Bundle Diameter (In.)	2.0
▪ Max. Bundle Diameter (mm)	51
▪ Min. Bundle Diameter (In.)	.50
▪ Min. Bundle Diameter (mm)	12.7
▪ Min. Loop Tensile Strength (Lbs.)	200
▪ Min. Loop Tensile Strength (N)	890
▪ Pricing Description	MLT Tie, 304 SS, Standard, 7.9" (201mm), .010" (.25mm) thk
▪ Thickness (In.)	.010
▪ Thickness (mm)	.25
▪ Tool	GS4MT, HTMT, PPTMT, ST2MT
▪ Min. Order UOM	PC
▪ Min. Order Qty.	50
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

[Home](#) | [Industries](#) | [Solutions](#) | [Products](#) | [Partners](#) | [Support](#) | [Contact Us](#) | [Site Map](#) | [Careers](#)

Copyright © 1995-2008, PANDUIT CORP. All rights reserved. | [Legal Information](#) | [Privacy Policy](#)