


## OPERATION INSTRUCTIONS


© Panduit Corp. 2016



## TOOL MAINTENANCE


TO INHIBIT CORROSION AND MAINTAIN PERFORMANCE OF THE TOOL, KEEP THE METAL SURFACES COATED WITH A LIGHT OIL (WD-40® OR EQUIVALENT).

**NOTE:** This precision tool has been engineered and designed for use with Panduit Pan-Steel Stainless Steel Ties. It is not intended for other uses such as cutting or tensioning other types of fastening devices.



## OPERATING INSTRUCTIONS

1. Loop tie around bundle and insert tip through head. Pull tie up snug on bundle by hand.
2. Place tool on tie as shown.
3. Squeeze handles as many times as necessary to tighten tie to the desired tension.
4. While maintaining final handle pressure from Step 3, rotate tool 1/4 to 1/2 turn until excess tail is cut off. Remove cut-off portion from tool.



# **PANDUIT**

## **STAINLESS STEEL CLAMP INSTALLATION TOOL**

### **Part No. ST2MT**

**FOR INSTALLING:  
Pan-Steel Stainless Steel Ties of  
Standard, Light-Heavy, Heavy and  
Extra-Heavy cross sections.**

**MADE IN USA**

**NOT INTENDED FOR MEDICAL USE.**  
User is responsible to determine suitability  
of product for intended use.

**REPLACEMENT KIT: (SOLD SEPARATELY)**  
KT2MG - Gripper Replacement Kit

**PANDUIT**  
[www.panduit.com](http://www.panduit.com)

For Technical Support:  
1-800-777-3300

E-mail: [techsupport@panduit.com](mailto:techsupport@panduit.com)