



TE Connectivity: Every Connection Counts
© 2016 TE Connectivity Ltd. family of companies. All Rights Reserved

+ IDENTIFICATION & LABELING

HEAT SHRINK MARKER SLEEVES



✓ Active

TE CONNECTIVITY (TE) HT-SCE-1/2-2.0-9

HT-SCE-1/2-2.0-9
TE Internal Number: 4117110001
Alias ID: 1193105-3

[EU RoHS Compliant](#)
[EU ELV Compliant](#)

Sleeve Length (Nominal) 50.8 mm [2 in]

Shrink Ratio 2:1

Recovered Inside Diameter (Max) 6.35 mm [.2499 in]

Expanded Inside Diameter (Min) 12.7 mm [.5 in]

Operating Temperature Range -55 – 225 °C [-67 – 437 °F]

DOCUMENTATION

Catalog Pages/Data Sheets

HT-SCE Heat Shrinkable Sleeves

PDF

English

Product Specifications

Product Specification

HT-SCE

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Format Ladder

Grade High Temperature

Product Type Marker Sleeve

Body Features

Shrink Ratio 2:1

Sleeve Color White

Material Radiation Crosslinked Fluoropolymer

Dimensions

Sleeve Length (Nominal) 50.8 mm [2 in]

Recovered Inside Diameter (Max) 6.35 mm [.2499 in]

Expanded Inside Diameter (Min) 12.7 mm [.5 in]

Compatible Cable Diameter 6.6 – 11.4 mm [.26 – .449 in]

Wall Thickness (Nominal) (Full Recovery) .38 mm [.015 in]

Usage Conditions

Operating Temperature Range -55 – 225 °C [-67 – 437 °F]

Operation/Application

Recommended Printer See Printer Ribbon Matrix

Recommended Ribbon See Printer Ribbon Matrix

Packaging Features

Packaging Quantity 250

Statement of Compliance

[Statement of Compliance](#)

PDF
