


## 114163-000 Product Details



**114163-000**

TE Part Number: 114163-000

 [Active](#)

 [Add to Part List](#)

### SolderSleeve Wire Splices

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- Sealing = Splash proof
- CMA (Min.-Max) = 3,600 - 5,000 CMA
- Wire Temperature Rating Range (Max.) = 85°C to 125°C

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

**NEW!**

### Documentation & Additional Information

#### Product Drawings:

- [SolderSleeve One-Step Wire Terminator, Low Temperature](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- [Wire and Cable, Harnessing and Protection Products](#) (PDF, English)

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Connection Type = Solder

#### Housing Related Features:

- Sealing = Splash proof
- CMA (Min.-Max) (CMA [mm<sup>2</sup>]) = 3,600 - 5,000 [1.80 - 2.50]

#### Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

#### Conditions for Usage:

- Wire Temperature Rating Range (Max.) = 85°C to 125°C
- Operating Temperature (Max.) (°C) = 125

#### Operation/Application:

- Application = Wire to Wire Splicing

#### Other:

- Brand = Raychem