

Search Results

- Evaluate
- FAQ's
 - Selection Guides
 - PDFConvenience..
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'P14-14R-E'

Your search criteria matched only one product, shown below

P14-14R-E



- Ring tongue design assures a secure connection in high vibration applications
 - Internal barrel serrations assure good wire contact and maximum tensile strength
 - Brazed seam protects terminal barrel from splitting during the crimp process
 - Barrel of terminal internally beveled to provide quick and easy wire insertion
 - Maximum recommended operating temperature 302°F (150°C)
 - UL and CSA rated up to 2000 V per UL 486A/B, where applicable
- ‡UL and CSA approved tooling/product combinations.
Note: Wire sizes #26 – #22 AWG, are not UL Listed or CSA Certified.

Part Number	P14-14R-E
RoHS Compliancy Status	Compliant
Part Description	Ring Terminal, 18- 14 AWG, 1/4" stud size, non-insulated.
Product Type	Terminals
CSA Certified	Yes
UL Listed	Yes
Length (In.)	0.91
Length (mm)	23.1
Width (In.)	0.46
Width (mm)	11.7
CE Compliant	No
Clearance	0.38
Clearance (mm)	9.7
Insulation	Non-Insulated
Panduit Color Code	No Color NonInsulated
Plating Type	Tinned
Pricing Description	Terminal Convenience Package
Stock	0.03
Stock (mm)	0.8
Stud Size	1/4"
Temperature Rating	302 Degrees Fahrenheit (150 Degrees Celsius)
Tool	CT-100A‡, CT-200‡, CT-600-A‡, CT-1570‡, CT-2500‡
Wire Range	18 – 14 AWG
Wire Range (mm ²)	1.0 – 2.5
Min. Order UOM	PC
Min. Order Qty.	20
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.