

Search Results

- Evaluate
 - FAQ's
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click  to remove) [Search Tips](#)  Within Results


 Text Search: 'HSTTV25-48-TL'

Your search criteria matched only one product, shown below

HSTTV25-48-TL



- Shrink ratio of 2:1 insulates a wide range of diameters and irregular shapes
 - Cross-linked, UV resistant material improves flame retardancy, chemical, and temperature resistance
 - Available in various colors for permanent, cost effective color coding
- Meets Mil Spec AMS-DTL-23053/5 Class 3.

Part Number	HSTTV25-48-TL
RoHS Compliant Status	Compliant
Part Description	Thin Wall Polyolefin Heat Shrink (UL224 VW1)
Material	Highly flame retardant polyolefin cross-linked^^
Color	Black
CSA Certified	Yes
Military Specification	AMS-DTL-23053/5 Class 3
UL Recognized	E122770
Length (ft.)	4
Length (m)	1.2
Flammability Rating	UL224 VW-1
Max. Recovered I.D. (In.)	.125
Max. Recovered I.D. (mm)	3.2
Min. Expanded I.D. (In.)	.250
Min. Expanded I.D. (mm)	6.4
Nominal Diameter (In.)	.250
Nominal Diameter (mm)	6.4
Nominal Recovered Wall Thickness (In.)	.025
Nominal Recovered Wall Thickness (mm)	0.6
Pricing Description	Heat Shrink Thin VW1, .25"(6.4mm) Dia, Black
Shrink Ratio	2:1
Temperature Range	-67°F to 257°F (-55°C to 125°C)
Min. Order UOM	PC
Min. Order Qty.	250
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.